

[Labels](#) / [Circuit Board Labels](#) / [Not for Wash Polyester Labels](#) /

3" Core Series WorkHorse Glossy Polyester Labels



# 3" Core Series WorkHorse Glossy Polyester Labels

**Part Number:**

THT-14-423-10

**Label/Tape Size:**

0.2 in H x 0.65 in W

**Material:**

Polyester

**Material Number:**

B-423

**Color:**

White

**For Use with Printer:**

BBP®81 Label Printer, BRADY IP® Series

Label Printer, BradyPrinter i7100,

BRADYPRINTER PR Plus Series Label Printer

[ADD TO CART](#)

1

## PEOPLE ALSO VIEWED

## OVERVIEW

Permanent Polyester (B-423) is ideal for electronic PCB and component identification, bar code labels, rating plates and solar panel identification.

- Glossy white finish with permanent acrylic is thermal transfer printable
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved; CSA accepted
- Meets requirements of a halogen-free material per DIN VDE 0472 part 815
- Service temperature of -94 to 230° F (-70 to 110° C)

## SPECIFICATIONS

Anti-Skid Surface?	N/A
Average Outdoor Durability	1 Year
Material Number	<b>B-423</b>
Corner Type	Rounded Corners
Dimensions	0.2 in H x 0.65 in W
UOM	Roll of 10000 Labels

Finish	Gloss
Indoor or Outdoor Use	Outdoor Use
Label/Tape Size	0.2 in H x 0.65 in W
Maximum Service Temperature °F	230 °F
Minimum Service Temperature °F	-94 °F
Overlamine B-Number	B-966B
Overlamine Included	Overlamine Not Included
Printable Area Dimensions	0.2 in H x 0.65 in W
Printable Area Height	0.2 in
Printable Area Width	0.65 in
Product Number	30120
UPC	662820301202
Quantity per Roll	10000
Quantity per Row	4
Secondary Label Included	Secondary Label is Not Included
Tamper Indication Type	N/A
Thickness	0.003 in
Trade Name	WorkHorse® ToughBond®
Adhesive Type	Acrylic
Applications	Asset Tracking, Barcode Labeling, Circuit Board ID - Through Hole Top, Component & Equipment ID, General & Industrial ID, Rating Plates
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer
Label/Media Format	Roll
Material	Polyester
Material Properties	N/A
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Rectangle
Suggested Ribbon Series	R4900, R6000, R6200

## Solutions

Floor Marking Guide  
GHS Label Compliance  
Lockout Tagout Compliance  
Arc Flash Labeling Requirements  
Cable and Wire Label Options  
Product and Barcode Labeling  
Brand Protection Solutions

## Services


Lockout Tagout Services  
Arc Flash Services  
Confined Space Services  
Visual Workplace Services  
Hazcom GHS Services  
Software Programming & Integration  
Label Template & File Conversion  
Printer Use & Training  
Printer Preventative Maintenance  
Toll and Custom Coating  
Authentication & Tracking Services

## Help

Contact Us  
Knowledge Center  
Printer Drivers & Firmware  
Brady Software Updates  
Safety Data Sheets  
Technical Data Sheets  
WEEE-RoHS Compliance  
Product Certification  
Printer Registration

## Resources

Find a Distributor  
Printer Selection Tool  
Label Selection Tool  
Digital Catalog  
Request a Catalog



**Brady (NYSE:BRC)** is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.

**Contact**  
6555 W. Good Hope Rd. Milwaukee WI 53223  
**Phone:** 888-250-3082  
**Hours:** 7am-6pm CST  
**Monday - Friday**

**About**  
[Corporation](#)  
[Privacy Policy](#)  
[Terms and Conditions](#)  
[Terms of Use](#)  
[ISO Certificates](#)

**Other**  
[Brady Sites](#)  
[Distributor Portal](#)  
[International Sites](#)  
[Safety Services](#)  
&  
[Software Smart ID Brand Protection](#)



© 2018 Brady Worldwide, Inc.