



WELCOME TO BRADY [My Account](#)
[Register/Login](#) **888-250-3082** [Contact Us](#)
[Find a Distributor](#)

[MY CART](#)

Enter Search Term or Part #

All Product Categories

[SEARCH](#)

[Home](#) [Products](#) [Labels and Tapes](#) [Labels](#) [Wire and Cable Labels](#) [Wire and Cable Labels](#) [TLS 2200®/TLS PC Link™ Labels](#) [EMAIL PAGE](#) [PRINT PAGE](#)



TLS 2200®/TLS PC Link™ Labels - # PTL-19-427-BL

SIZE: 1.000" W x 1.000" H (25.400 mm W x 25.400 mm H)
MATERIAL: Self-Laminating Vinyl
QTY/UOM: 250/Roll
CATALOG #: PTL-19-427-BL
PRODUCT #: 18648

Questions?
1.888.250.3082

[VIEW LARGER](#)



[OVERVIEW](#) [SPECIFICATIONS](#)

Specification Of TLS 2200®/TLS PC Link™ Labels

Application(s): Communications Cables, Laboratory Identification, Panel Identification, Voice/Data Identification, Wire & Cable Marking

Agency: UL Recognized

Approval(s)/Compliance:

Size: 1.000" W x 1.000" H (25.400 mm W x 25.400 mm H)

Printable Area: 1.000" W x 0.375" H (25.400 mm W x 9.530 mm H)

Max Characters Per Line For Font #2: 24

Max Lines of Text For Font #2: 3

Label Type/Style: Self-Laminating Label

Color: Blue/Translucent

Wire Gauge: 12 to 10

Finish: Matte

Qty Per Row: 1

Material Type: Vinyl

Material Description: Self-Laminating Vinyl

Brady Material #: [B-427](#)

Safety Catalog: [pg. 278](#)

General ID Catalog: [pg. 57](#)

Recommended Ribbon Series: R4310

Acceptable Ribbon Series: R6210

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Special Properties: Excellent abrasion and smudge resistance, Excellent water & oil resistance, Self-Extinguishing, Self-Laminating

RoHS Compatibility: Pass 2002/95/EC

QTY/UOM: 250/Roll

Customer & Tech Support

[Find a Distributor](#)
[Submit Product Feedback](#)
[Submit Website Feedback](#)
[Contact Us](#)
[Site Map](#)

Distribution Partners

[Bradyserve.com](#)
[BradyDistributor.com](#)
[Minimum Advertised Price Policy](#)

Corporate Info

[About Brady](#)
[Bradycorp.com](#)
[Privacy Policy](#)
[Legal Information](#)
[ISO14001 Certified](#)
[ISO9001 Certified](#)
[Terms of Use](#)
[Terms and Conditions of Sale](#)

Brady International Sites

[Canada](#) [Brazil](#) [Europe, Africa, Middle East](#)
[Canada \(Français\)](#) [Asia](#)
[Latin America](#) [Australia](#)



high-performance materials clearly identify products, components and other assets, even in the most extreme conditions.

©2014 Brady Worldwide, Inc.



Safe & Secure Online Shopping