

- ? [About Brady](#)
- ? [ISO 9001](#)
- ? [Contact Us](#)
- ? [Request A Catalog](#)
- ? [Send Product Feedback](#)

- ? [Where to Buy](#)
- ? [Join Our Mailing List](#)


PRODUCT, FACILITY, & SAFETY IDENTIFICATION SOLUTIONS

COUNTRY/REGION

- WHAT'S NEW
- PRODUCTS BY CATEGORY
- PRODUCTS BY INDUSTRY
- SERVICES
- SUPPORT
- REGULATIONS/ COMPLIANCE
- LEAN MANUFACTURING & MAINTENANCE
- PRODUCT REGISTRATION

Home [Products By Category](#) [Labels](#) [Pre-Printed Labels](#) [Wire & Cable Markers](#)
[Wire Marker Cards](#) [Standard Numbers & Letters](#) [TLS 2200®/TLS PC Link™ BradyBondz™ Labels](#)

TLS 2200®/TLS PC Link™ BradyBondz™ Labels




Labels for the TLS 2200® & TLS PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL & CSA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to

[Click for larger Image](#)

Overview

Specifications

<p>Catalog #: PTL -39-430</p> <p>Product #: 18675</p> <p>Description: TLS 2200®/TLS PC Link™ BradyBondz™ Labels</p> <p>Size: 0.375" W x 0.600" H (9.530 mm W x 15.240 mm H)</p> <p>Printable Area: 0.375" W x 0.600" H (9.530 mm W x 15.240 mm H)</p> <p>Brady Material #: B-430</p> <p>Material Description: Clear Polyester</p> <p>Suggested Ribbon Part#: R6010</p> <p>General ID Catalog: pg. 25</p> <p>Application(s): 1-6 Outlet Faceplates, General Identification Panel Identification, Through Hole- Top, Voice/Data Identification</p> <p>QTY/UOM: 750/Roll</p> <p>MSRP (US\$)*: \$52.91</p>	<p>RELATED INFORMATION</p> <ul style="list-style-type: none"> Cable Management Software Label Software TIA/606A Quick Reference Guide TIA/606A Compliant Labeling Spec DataComm Cross Reference Guide Voice Data Materials Chart Label Templates Contact DataComm Specialist DataComm Brochure
--	--



For more information on this product, contact Brady Customer Service or an Authorized Brady Distributor. Brady products are sold through distribution. Click on the "Find a Distributor" button to find a distributor near you.

*If you're not based in US, please contact your local Brady office for correct pricing.

For Distributors: [BradyDistributor.com](#) | [Bradyserve.com](#)
 Additional Information: [Privacy](#) | [Copyright](#) | [Site Map](#)