



HELP ▾

888-250-3082



US - ENGLISH ▾

SIGN IN ▾



Search by Part # or Keyword



- LABELS
- PRINTERS
- TAPE
- LOCKOUT TAGOUT
- SOFTWARE
- SIGNS
- PIPE & VALVE
- TAGS
- ABSORBENTS

[Search Only Products](#) / Solid Numbers Wire Marker Card

# Solid Numbers Wire Marker Card




Solid Numbers Wire Marker Card

\$56.49 (USD) / pack of 25 sheets

[Overview Specifications](#)





### Product Highlights:

**Material:** Cloth

**Dimensions:** 0.75 in H x 0.25 in W

**UOM:** Pack of 25 Sheets

**Color:** Black on White

**\$56.49** (USD) / pack of 25 sheets

**Part Number:** WM-1-SC-PK

1


ADD TO CART

 [Add To Favorites](#)


People Also Viewed




Consecutive Numbers Wire Markers  
**\$50.49 (USD)**




Pre-printed 1 Wire Markers  
**\$50.49 (USD)**



Terminal Wire Markers  
**\$50.49 (USD)**




Consecutive Numbers Repeated Wire Markers  
**\$50.49 (USD)**



Wire Marker Cards Value Pack  
**\$11.99 (USD)**



Consecutive Numbers Repeated Wire Markers  
**\$50.49 (USD)**



Consecutive Numbers on Color Backgrounds Wire Markers



3" Core Series ToughBond Glossy Polyester Labels



WARNING Electrical Hazard Authorized Personnel Only



3" Core Series WorkHorse Glossy Polyester Labels



---

## Overview

B-500 Repositionable Vinyl Cloth wire markers from Brady® are perfect for your general wire marking needs.

- Card-mounted wire markers allow for quick, on-the-spot wire marking
- Brady B-500 Repositionable Vinyl Cloth holds tightly to surfaces but allows item to be repositioned with ease if necessary
- Excellent flexibility for wrapping around curved surfaces
- Withstands moderate heat, oil, water and dirt

---

## Specifications

Material Number	<b>B-500</b>
Calculated Country Of Origin	MX - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own

	risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Cards or Sheets per Pack	25
Catalog Page #	<a href="#">220</a>
Dimensions	0.75 in H x 0.25 in W
UOM	Pack of 25 Sheets
Finish	Matte
Maximum Service Temperature °F	176 °F
Minimum Service Temperature °F	-40 °F
National Stock Number (NSN)	9905003667368
Product Number	111926
UPC	662820909583
Quantity per Card or Sheet	72
Thickness	0.0088 in
Adhesive Type	Repositionable Rubber
Applications	Cable & Wire Marking

Color	Black on White
Label/Media Format	Die-Cut on Cards
Label Properties	Repositionable Labels
Material	Cloth
Printer and Label Applications	Wire & Cable
Resistance Properties	Abrasion-Resistant, Corrosion-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant, Water-Resistant, Weather-Resistant
Serialization	No Serialization
Text Legend	1

## Solutions

[Floor Marking Guide](#)  
[GHS Label Compliance](#)  
[Lockout Tagout Compliance](#)  
[Arc Flash Labeling Requirements](#)  
[Cable and Wire Label Options](#)  
[Product and Barcode Labeling](#)

## Services

[Lockout Tagout Services](#)  
[Arc Flash Services](#)  
[Confined Space Services](#)  
[Software Programming & Integration](#)  
[Label Template & File Conversion](#)  
[Printer Use & Training](#)  
[Printer Preventative Maintenance](#)  
[Toll and Custom Coating](#)  
[Authentication & Tracking](#)

## Help

[Contact Us](#)  
[Website Feedback](#)  
[Knowledge Center](#)  
[Printer Drivers & Firmware](#)  
[Brady Software Updates](#)  
[Safety Data Sheets](#)  
[Technical Data Sheets](#)  
[WEEE-RoHS Compliance](#)  
[Product Certification](#)  
[Printer Registration](#)

## Resources

[Find a Distributor](#)  
[Design Custom Safety Signs](#)  
[Create Custom THT Labels](#)  
[Printer Selection Tool](#)  
[Label Selection Tool](#)  
[Digital Catalog](#)  
[Request a Catalog](#)  
[Interactive Facility Map](#)  
[EPA e-Manifest Update](#)

**Corporate**

- [About](#)
- [Careers](#)
- [Investors](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)
- [Terms of Use](#)
- [ISO Certificates](#)

**Other Brady Sites**

- [Distributor Portal](#)
- [International Sites](#)
- [Safety Services & Software](#)
- [Brand Protection Solutions](#)

**Contact**

6555 W. Good Hope Rd.  
Milwaukee, WI 53223  
Phone: 888-250-3082  
Hours: 7am-6pm CT  
Monday - Thursday;  
Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 © Brady Worldwide, Inc.