



Datasheet for part number MS3101E16-9P

| |
|---|
| Our Catalog Part Number: MS3101E169P |
| Our Global Manufacturing Part Number: 024232-0013 |
| Brand: Cannon Product Category: Circular Product Line: MIL-DTL 5015 Series I Series: MIL-C-5015 |

| Product Datasheet | |
|--|---|
| Thread | Connector with threaded coupling |
| Shell Style | Cable connecting plug |
| Endbell Style | Endbell with clamp and bushing |
| Gender | Pin |
| Shell Size | 16 |
| Contact Arrangement | 16-9 |
| Number of contacts | 2 contacts size 12, 2 contacts size 16 |
| Contact Type | Solder Cup |
| Contact Plating | Hard silver |
| Contacts installed | yes |
| Shielding | no |
| Contact Rating at +20 °C (68 °F) (Size 15/15S/16/16S) | 22 A |
| Contact Rating at +20 °C (68 °F) (Size 25/12) | 41 A |
| Contact Resistance (Size 15/15S/16/16S) | 6 mΩ |
| Contact Resistance (Size 25/12) | 3 mΩ |
| Operating Voltage | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41. |
| Insulator Resistance | Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ |
| Test Voltage | 1600 Vrms |
| Air and Creepage Paths (Min) | 1,1 mm |
| Ambient Temperature | Standard insulator material -55°/+125°C (-67/257°F) |
| Safety Provisions | IP65 acc. to DIN 40 050 |
| Salt Spray Resistance | 500 hours salt spray resistant |
| Mating Cycles | 500 min |
| Sep. Force per Contact (Size 15/15S/16/16S) | 1,0 N |
| Sep. Force per Contact (Size 25/12) | 1,5 N |
| Gage | For infos on Gage please see catalog VG95234, part 1 |
| Coupling Torque | Closing: 5,5 Nm max / Opening: 0,46 Nm min |
| Contact Retention (Size 15/15S/16/16S) | 35 N |
| Contact Retention (Size 25/12) | 55 N |
| Shell Material | Aluminium alloy |
| Shell Plating | Olive drab chromate coating over cadmium plating |
| Insulator and Gromet Material | Neoprene |
| Contact Material | Copper alloy |
| Harnessing Info: Contact Cross-Section | See assembly instruction |
| Harnessing Info: Insulator Diameter | See assembly instruction |

Specifications and dimensions subject to change.



Datasheet for part number MS3101E16-9P

| |
|---|
| Our Catalog Part Number: MS3101E169P |
| Our Global Manufacturing Part Number: 024232-0013 |
| Brand: Cannon Product Category: Circular Product Line: MIL-DTL 5015 Series I Series: MIL-C-5015 |

| | |
|--|---|
| Product Datasheet | |
| Wire Stripping (Size 15/15S/16/16S) | 6,2 mm |
| Wire Stripping (Size 25/12) | 6,2 mm |
| General Info | <i>All tests in accordance with VG95319 and/or if applicable with VG95210</i> |