

- INSULATOR: GLASS FILLED PLASTIC UL 94 V-0 RATED, GREY RAL 7035
- CONTACTS: COPPER ALLOY, PLATING: 0,8 µM GOLD OVER NICKEL

- CONTACTS 5-16 TO ANY OTHER CONTACT WITHIN THIS GROUP: 0,7 MM
- CONTACT 25 TO 26: 5,5 MM

6. CONNECTOR IS PART MARKED: **PART-NO. CONEC ABC**



|          |                                         |      |                |          |
|----------|-----------------------------------------|------|----------------|----------|
| 14       | Signal contact (Pos. 5-16,27,32)        | 3    |                |          |
| 8        | Power contact (Pos. 25,26,28-31, 33,34) | 2    |                |          |
| 1        | Case 34pos. female                      | 1    |                |          |
| quantity | part description                        | item | dwg no. / norm | material |

|                                                                                                                                                                       |          |                                                                                                                                                                               |                                                                                |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER AND NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.<br>OWNERSHIP AND COPYRIGHT OF CONEC GmbH |          | partist                                                                                                                                                                       |                                                                                |
|                                                                                                                                                                       |          | finish: see notes<br>tolerance ISO 2768-m<br> scale: 2,5:1 (10:1)<br>material: see notes |                                                                                |
| DO NOT ALTER CAD DRAWING BY HAND                                                                                                                                      |          | date<br>05.10.05<br>name<br>Mankopf                                                                                                                                           | title:<br><b>FEMALE CONNECTOR 22pos.</b><br>SOLDER PIN STRAIGHT<br>AdvancedTCA |
|                                                                                                                                                                       |          | appd. 05.10.05<br>Kühle                                                                                                                                                       |                                                                                |
|                                                                                                                                                                       |          | norm                                                                                                                                                                          |                                                                                |
|                                                                                                                                                                       |          | d-old                                                                                                                                                                         |                                                                                |
|                                                                                                                                                                       |          |                                                                                          |                                                                                |
| dwg no:                                                                                                                                                               | Inventor | DIN-A2<br>sh:1                                                                                                                                                                |                                                                                |
| rev. description date name                                                                                                                                            | part no: | ATC22W08FGRCS5X                                                                                                                                                               |                                                                                |