


3SBC1527A2 Product Details

SharePrintEmail



3SBC1527A2
(3 - 1617072 - 2)

TE Internal Number: 3 - 1617072 - 2

Active

Military/Aerospace High Performance Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- ? 3SBC 1/5 - Size Relay Series

? Input Voltage = 26.5 VDC

? Contact Arrangement = 2 Form C, DPDT, 2 C/O

? Contact - Rated Current = 2 A

? Non Polarized, Monostable Coil - Magnetic System

View all Features

Quick Links

- ? Check Pricing & Availability

? Search for Tooling

? Product Feature Selector

? Contact Us About This Product

Documentation & Additional Information	
Product Drawings: ? None Available Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling
Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Series = 3SBC 1/5 - Size Relay ? Termination Type = Solder Hook Terminals Electrical Characteristics: ? Input Voltage (VDC) = 26.5 ? Contact - Rated Current (A) = 2 ? Coil Polarity Protection Diode = Without ? Transistor Driver = Without ? Coil Resistance (?) = 1350 ? MOSFET Driver = Without ? Coil Power Measurement = Milliwatts ? Coil - Rated Power (mW) = 520 ? Actuating System = DC ? Shock = 75 G's, 6ms ? Vibration = 30G's, 10 to 3000Hz Contact Features: ? Mounting Options = Chassis Mount ? Enclosure Type = Hermetically Sealed	Configuration Features: ? Contact Arrangement = 2 Form C, DPDT, 2 C/O ? Coil - Magnetic System = Non Polarized, Monostable ? Coil Suppression Diode = Without Industry Standards: ? Government/Industry Qualification = Yes ? Government/Industry Part Number = M39016/13 -066M ? RoHS/ELV Compliance = Not ELV/RoHS compliant ? Lead Free Solder Processes = Not suitable for lead free processing ? Approved Standards = M39016 Qualified, M Level Conditions for Usage: ? Temperature Range (°C) = -65 - +125 Other: ? Brand = CII

Corporate Information

Who We Are

Investors

News Room

Supplier Portal

Careers

Quick Links

Check Distributor Inventory

Cross Reference

Find Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us

Find a Phone Number

Search Knowledge Base

Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

