


FCA-125 -24 Product Details

Share Print Email



FCA-125 -24
(3 - 1617748 -0)

TE Internal Number: 3 - 1617748 -0

 [Active](#)

Military/Aerospace Mid - Range Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? FCA 10 -25 Amp Relay Series
- ? DC Actuating System
- ? Coil - Rated Voltage = 28 VDC
- ? Contact Arrangement = 1 Form C, SPDT, 1 C/O
- ? Current Rating = 25 A

[View all Features](#)

Quick Links

- ? [Check Pricing & Availability](#)
- ? [Search for Tooling](#)
- ? [Product Feature Selector](#)
- ? [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? [RELAY](#) (PDF, English)

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Series = FCA 10 -25 Amp Relay
- ? [Terminal Configuration](#) = Solder Hook

Electrical Characteristics:

- ? [Actuating System](#) = DC
- ? [Coil - Rated Voltage \(VDC\)](#) = 28
- ? [Current Rating \(A\)](#) = 25

Termination Features:

- ? [Terminal Plating](#) = Tin -Lead
- ? Auxiliary Contacts = Without

Body Features:

- ? [Mount Type](#) = Side Mount

Configuration Features:

- ? [Contact Arrangement](#) = 1 Form C, SPDT, 1 C/O
- ? [Coil Suppression Diode](#) = With
- ? Coil - Magnetic System = Polarized, Monostable

Industry Standards:

- ? Government/Industry Qualification = Yes
- ? Government/Industry Part Number = M6106/19 -024
- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not suitable for lead free processing

Other:

- ? Brand = CII

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

