

Datasheet

Item No. Z7.268.0327.0

Jumper bar IVB WKF 1,5- 3

Cross connector, insulated for DIN rail terminal blocks type WKF..., 3 -pole



Item No.	Z7.268.0327.0
EAN	4015573732018
order unit	10 Piece(s)

Technical data

**Accessories**

Colour	Yellow
Type	Cross connector
Modular spacing	4.2 mm
Number of bridged clamps	3
Mounting method	Pluggable
Insulated	Yes

Drawings

Insolierung  
gelb/  
insulation  
yellow

**Z7.268.0227.0**  
M 1:1

Weitere Daten siehe Katalog  
further data see catalog

Teile-Nr. part-number	Typ type	Polzahl pole	L
Z7.268.0227.0	IVB WKF 1,5- 2	2	7,0
Z7.268.0327.0	IVB WKF 1,5- 3	3	11,2
Z7.268.0427.0	IVB WKF 1,5- 4	4	15,4
Z7.268.0527.0	IVB WKF 1,5- 5	5	19,6
Z7.268.1027.0	IVB WKF 1,5-10	10	40,6
Z7.268.2027.0	IVB WKF 1,5-20	20	82,6

Freitoleranz nach DIN	CAD - Zeichnung, keine manuellen Änderungen	1. Verwendung: -	Bl.: 1 von 1												
Maßstab: 5:1	Werkstoff und Oberfläche:	Zeichnung Nr. T Z7.268.0227.0 01K	Index												
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td>2004</td> <td>Tag</td> <td>Nome</td> </tr> <tr> <td>Entworfen</td> <td>09.11.</td> <td>Schmitt J.</td> </tr> <tr> <td>Gepüßt</td> <td>-</td> <td>-</td> </tr> <tr> <td>Normgepr.</td> <td>-</td> <td>-</td> </tr> </table>		2004	Tag	Nome	Entworfen	09.11.	Schmitt J.	Gepüßt	-	-	Normgepr.	-	-	Ersatz für: -	
2004	Tag	Nome													
Entworfen	09.11.	Schmitt J.													
Gepüßt	-	-													
Normgepr.	-	-													
<p><b>wieland</b> Elektrische Verbindungen</p>		<p><b>VERBINDUNGSSTECKER</b> insulated jumper bar</p>													
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td>Typ</td> <td>Benennung</td> </tr> <tr> <td>IVB</td> <td></td> </tr> <tr> <td>WKF 1,5-..</td> <td></td> </tr> </table>		Typ	Benennung	IVB		WKF 1,5-..									
Typ	Benennung														
IVB															
WKF 1,5-..															

Z72680227001K\_4\_CADWZ8\_Schmitt\_2004-11-09T15:33:52\_1:000