



Quality Products. Service Excellence.

Welded Steel 2-Post Rack *RB-2P Series*

UL 2416 Rated 1,000 lbs|454 kg Weight Capacity



RACK BASICS®



Features

- Constructed in 12-gauge steel.
- 19" EIA-310-D compliant 10-32 double-tapped rails.
 - Includes marked rack unit dividers to aid in equipment mounting.
- Don't forget to order your **Mounting Hardware**.
- Side ganging and accessory mounting holes.
- Includes two (2) pairs of integrated 10-32 ground studs, spaced 5/8" apart. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, a pair is located near the top of the rack, while the other at lower side.
- UL Listed 2416 rated for up to 1,000 lbs (454 kg) static load rating.
- Finished in satin black powder paint.
- Rails and Base packaged in cardboard to prevent freight damage.
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.

Part of the Rack Basics® line of economy rack solutions.

Gallery



Accessories

- High-Density Vertical Finger Manager with Slam-Latching Door
- Universal Rack Shelf
- Vertical Finger Cable Manager with Door
- Top Wire Management
- Top Cable Chimney
- Two-Post Extension Support Bracket
- Horizontal Ring Cable Manager
- Horizontal Finger Cable Manager
- Grounding
- Rack Isolation Kit
- Vertical Rack Cable Manager with Door
- Two Post Mounting Adjustable Shelf
- Rack Panels
- Two Post Centered Shelf
- Two Post Mounting Deep Channel Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- 10-32 Mounting Hardware
- Outlet Strips
- Open Frame Rack Caster Kit
- Rack and Cabinet Baying/Ganging/Joining Kit

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
RB-2P24	48.12	20.46	15.00	24U	42.16	19.00

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
RB-2P77	83.12	20.46	15.00	44U	77.12	19.00
RB-2P84	90.12	20.46	15.00	48U	84.16	19.00

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack** *Data subject to change without notice*

© 2019. Hammond Manufacturing Ltd. All rights reserved.