



**2X2 Flush FRPT, One-Piece Units (PT2X2FIT)**

Description	Color	Catalog No.	Description	Color/Material	Catalog No.
2X2 Poke-Through Non-metallic Cover	Black	<b>PT2X2BL</b>	2X2 Poke-Through	Black/Brass	<b>PT2X2BRS3</b>
	Gray	<b>PT2X2GY</b>		Brass Finish/Brass	<b>PT2X2BRS</b>
	Black	<b>PT2X2IGBL*</b>		Black/Brass	<b>PT2X2IGBRS3*</b>
	Gray	<b>PT2X2IGGY*</b>		Brass Finish/Brass	<b>PT2X2IGBRS*</b>
<ul style="list-style-type: none"> <li>Pre-wired 20A duplex Style Line® receptacle and (2) Category 5e data jacks</li> <li>Painted aluminum flange</li> <li>Approved for use in the City of Chicago</li> </ul>			<ul style="list-style-type: none"> <li>Pre-wired 20A duplex Style Line® receptacle and (2) Category 5e data jacks</li> <li>Solid brass flange</li> <li>Approved for use in the City of Chicago</li> </ul>		
 <p>PT2X2GY</p>			 <p>PT2X2BRS3</p>		

Note: \*Includes pre-wired 20A isolated ground duplex Style Line® receptacle.

**2X2 Flush FRPT, Two-Piece Units**

Description	Catalog No.
Multi-Channel Through-Floor Fitting with (1) 3/4 in. E.M.T. stem with junction box for power and (2) 1/2 in. E.M.T. stems for low voltage.	<b>PT2X2FIT</b>
	<p>Specifications:</p> <ul style="list-style-type: none"> <li>1 – 4 hour fire rating (1 – 3 hour for steel floor units and concrete topping, D900 Series Design)</li> <li>For 2 1/4 in. to 7 in. floor thickness</li> <li>UL installation spacing – minimum 2 ft. on center and not more than one per 65 sq. ft. of floor area</li> <li>Approved for use in the City of Chicago</li> </ul>

**Service Fittings**

Description	Color	Catalog No.	Description	Color/Material	Catalog No.
2X2 Service Fitting Non-metallic Cover	Black	<b>PT2X2SFBL</b>	2X2 Poke-Through Non-metallic Cover	Black/Brass	<b>PT2X2SFBR3</b>
	Gray	<b>PT2X2SFGY</b>		Brass Finish/Brass	<b>PT2X2SFBR</b>
<ul style="list-style-type: none"> <li>Pre-wired 20A duplex Style Line® receptacle and (2) Category 5e data jacks</li> <li>Painted aluminum flange</li> </ul>			<ul style="list-style-type: none"> <li>Pre-wired 20A duplex Style Line® receptacle and (2) Category 5e data jacks</li> <li>Solid brass flange</li> </ul>		
 <p>PT2X2SFBL</p>			 <p>PT2X2SFBR3</p>		

**Accessories**

Description	Color/Material	Catalog No.
Non-Metallic Replacement Covers	Brass Finish	<b>PT2X2CBRS</b>
	Black	<b>PT2X2CBL</b>
	Gray	<b>PT2X2CGY</b>
 <p>PT2X2CBL</p>		

Note: See page Q28 for 3 inch closure plug.



Complies with UL514 A & C