

This page is "Products".

## Skip Navigation

- ? [Text](#)
- ? [Retrieval in site](#)
- ? [Global Navigation](#)
- ? [Site Information](#)

USA

- ? [Site Map](#)
- ? [Contact Us](#)

Search

## Main Navigation

- ? [Home](#)
- ? [Products](#)
- ? [Product Support](#)
- ? [Technology & Solutions](#)
- ? [About IDEC](#)
- ? [News & Events](#)
- ? [Jobs & Careerss](#)
- ? [World IDEC](#)

USA

## Category

### Products

## The text starts here.

[Home](#) > [Products](#) >

- ? 

Overview

[Overview](#)
- ? 

Product List

[Product List](#)
- ? 

Documents & Downloads

[Documents & Downloads](#)
- ? 

Additional Information

[Additional Information](#)

### HW1F -31F11QD -Y-6V

[IEC style industrial switches, pilot devices and EStops]



HW1F -31F11QD -Y-6V

**Price\*** \$52.95 [Check Store Now](#)

#### Note

Note: All pricing is USA suggested retail.



#### Product Specifications

|                                |                                                          |
|--------------------------------|----------------------------------------------------------|
| Status                         | Active                                                   |
| Mounting Hole Size             | ? 22mm                                                   |
| Operator Function              | Selector Switch Illuminated                              |
| Operator Details               | Spring Return from Right                                 |
| Bezel Type                     | Plastic                                                  |
| Bezel Height                   | Standard                                                 |
| Bezel Shape                    | Round                                                    |
| Handle Type                    | Knob                                                     |
| Handle Color                   | Yellow                                                   |
| Number of Positions            | 3                                                        |
| Illumination Style             | Full Voltage                                             |
| Illumination Voltage           | 6V DC, 6V AC                                             |
| Lamp Type                      | LED                                                      |
| Contact Block Termination Type | Finger Safe Screw Terminal                               |
| Contact Rating (General)       | 10A                                                      |
| Normally Open Contacts         | 1                                                        |
| Normally Closed Contacts       | 1                                                        |
| Contact Form                   | SPST                                                     |
| Contact Material               | Silver                                                   |
| Ingress Protection Rating      | IP65 (Oiltight)                                          |
| Construction Type              | Removable Contact Block Assembly, Snap-on Contact Blocks |
| Product Series Name            | HW Series                                                |

#### Automation

- ? [PLCs](#)
- ? [Operator Interface](#)
- ? [Automation Software](#)
- ? [Power Supplies](#)
- ? [Sensors](#)
- ? [Communication & Networking](#)

#### Safety

- ? [E-Stops](#)
- ? [Door Interlock Switches](#)
- ? [Enabling Switches](#)
- ? [Relay Barriers](#)
- ? [AS-i Safety at Work](#)

#### Switching & Controls

- ? [Switch & Pilot Devices](#)
- ? [Display Lights](#)
- ? [Relays & Sockets](#)
- ? [Timers](#)
- ? [Terminal Blocks](#)
- ? [Circuit Breakers](#)
- ? [IEC Contactors](#)

## Page Navigation

[Back to top](#)

## Local Navigation

#### Resources

- [Product Support](#)
- [Stock check](#)
- [Distributor Locator](#)
- [IDEC Sales Locator](#)
- [Catalog PDFs](#)
- [Mature Product List](#)
- [Master Price List](#)
- [Contact Us](#)

## BannerArea



## Site Information