

This page is "Products".

Skip Navigation

- ? [Text](#)
- ? [Retrieval in site](#)
- ? [Global Navigation](#)
- ? [Site Information](#)

USA

- ? [Site Map](#)
- ? [Contact Us](#)

Main Navigation

- ? [Home](#)
- ? [Products](#)
- ? [Product Support](#)
- ? [Technology & Solutions](#)
- ? [About IDECE](#)
- ? [News & Events](#)
- ? [Jobs & Careerss](#)
- ? [World IDECE](#)

USA

Category

Products

The text starts here.

[Home](#) > [Products](#) >

- ? [Overview](#)
- ? [Product List](#)
- ? [Documents & Downloads](#)
- ? [Additional Information](#)

HW1B -M1F40 -R

[IEC style industrial switches, pilot devices and EStops]



HW1B -M1F40 -R

Price* \$38.85

[Check Store Now](#)

Note

Note: All pricing is USA suggested retail.



Product Specifications

Status	Active
Mounting Hole Size	? 22mm
Operator Function	Pushbutton
Operator Details	Momentary
Bezel Type	Plastic
Bezel Height	Standard
Button Style	Flush
Button Shape	Round
Button Color	Red
Contact Block Termination Type	Finger Safe Screw Terminal
Contact Rating (General)	10A
Normally Open Contacts	4
Normally Closed Contacts	0
Contact Form	SPST
Contact Material	Silver
Ingress Protection Rating	IP65 (Oiltight)
Construction Type	Removable Contact Block Assembly, Snap-on Contact Blocks
Product Series Name	HW Series

Automation

- ? [PLCs](#)
- ? [Operator Interface](#)
- ? [Automation Software](#)
- ? [Power Supplies](#)
- ? [Sensors](#)
- ? [Communication & Networking](#)

Safety

- ? [E-Stops](#)
- ? [Door Interlock Switches](#)
- ? [Enabling Switches](#)
- ? [Relay Barriers](#)
- ? [AS-i Safety at Work](#)

Switching & Controls

- ? [Switch & Pilot Devices](#)
- ? [Display Lights](#)
- ? [Relays & Sockets](#)
- ? [Timers](#)
- ? [Terminal Blocks](#)
- ? [Circuit Breakers](#)
- ? [IEC Contactors](#)

Page Navigation

[Back to top](#)

Local Navigation

Resources

- [Product Support](#)
- [Stock check](#)
- [Distributor Locator](#)
- [IDECE Sales Locator](#)
- [Catalog PDFs](#)
- [Mature Product List](#)
- [Master Price List](#)
- [Contact Us](#)

BannerArea



Site Information

(C)2008 IDECE Corporation, All rights reserved.