

699 / 899 GP Series - Single Row Terminal Blocks



699 GP 06

Specifications

- A Kulka® Brand
- 20 amps
- 300 Volts AC/DC, Class B
- 150 Volts AC/DC, Class C
- 899 series (riveted construction) 150 Volts AC/DC, Class C
- Base, phenolic, 150°C (UL RTI)
- JJ (GDI-30F) material available
- Screws, steel, #6-32 phil-slot
- Terminals, plated brass
- Open back design (Insulator strip required for voltage rating - [Reference](#))
- 1-23 poles at 7/16" centers
- Accepts lugs w/max width of .33"
- Bare wire range #14-#20 AWG

Standards

- UL recognized file no. XCFR2.E47811
- CSA certified file no. LR19766
- CE Compliant (IEC 60947-7-1)
- RoHS compliant

[Product Datasheet](#)

Single Row Terminal Blocks - 699 / 899 GP Series

Catalog #	# of Poles	Dimensions	
		A	B
699 GP 01	1	1.19	0.88
699 GP 02	2	1.62	1.31
699 GP 03	3	2.06	1.75
699 GP 04	4	2.50	2.19
699 GP 05	5	2.94	2.63
699 GP 06	6	3.37	3.06
699 GP 07	7	3.81	3.50
699 GP 08	8	4.25	3.94
699 GP 09	9	4.69	4.38
699 GP 10	10	5.12	4.81
699 GP 11	11	5.56	5.25
699 GP 12	12	6.00	5.69
699 GP 13	13	6.44	6.13
699 GP 14	14	6.87	6.56
699 GP 15	15	7.31	7.00
699 GP 16	16	7.75	7.44
699 GP 17	17	8.19	7.88
699 GP 18	18	8.62	8.31
699 GP 19	19	9.06	8.75
699 GP 20	20	9.50	9.19
699 GP 21	21	9.94	9.63
699 GP 22	22	10.37	10.06
699 GP 23	23	10.81	10.50


mm = dim X 25.4

Hardware Options

(Hardware options may affect ratings - Consult Customer Service)

Catalog #	Product Description	Reference Sheet
KT46	Full Quick Connect (0 degree Flat)	Reference
KT47	Full Quick Connect (45° Bend)	
KT48	Full Quick Connect (90° Bend)	
KT52	Half Quick Connect (0° Flat)	
KT53	Half Quick Connect (45° Flat)	
KT54	Half Quick Connect (90° Flat)	Reference
3/4 ST	Half Solder	
Z	Lug over the Side (.437)	Consult Customer Service
J 601	Line-to-Line Jumper	Reference
601RJ(S)	Multiple Position Jumper	
2102	Stud	Reference
2104	Feed Thru Solder	
2120	Solder Pin	
2121	Solder Pin	
PSB	Phil-Slot Brass Screw	Consult Customer Service
	Marking Strips & Insulator Strips - Sub-Mounted	Reference

Quick Connects: .032" x .250"



CONTACT

Marathon Special Products
427 Van Camp Road

LINKS

[About Us](#)

ABOUT

Marathon Special Products is an industry leader for supplying power blocks, terminal blocks, and fuse holders in North

P.O. Box 468
Bowling Green, Ohio 43402

tel: 419-352-8441
fax: 419-352-0875
email: marketing@marathonsp.com

CUSTOMER SERVICE HOURS

Mon-Fri 8am-5pm EST

Contact Us

Terms & Conditions

Locate a Distributor

America. We've achieved this by providing one of the broadest line offerings with various sizes, terminal styles, electrical ratings and features.

