

- [About Leviton](#)
- [A Century of Success](#)
- [Press](#)
- [Join Our eMailing List](#)
- [Trade Shows](#)
- [RoHS](#)
- [Career Opportunities](#)
- [Contact Us](#)
- [All Leviton Products](#)
- [Electrical](#)
- [Network Solutions](#)
- [Lighting Controls](#)
- [Entertainment](#)
- [Home Automation](#)
- [Connected Home](#)
- [Energy Management](#)
- [Power Quality](#)
- [Library Home](#)
- [Application Notes](#)
- [Brochures / Catalogs](#)
- [Case Studies](#)
- [DDLs](#)
- [Downloads](#)
- [Drawings](#)
- [Line Cards](#)
- [Manuals / Instructions](#)
- [Product Specifications / Datasheets](#)
- [Software](#)
- [Specs \(AIA / CSI\)](#)
- [Take One](#)
- [Tech Notes](#)
- [Technical Articles](#)
- [Videos](#)
- [ez-Biz](#)
- [ez-Find](#)
- [ez-Learn](#)
- [ez-Configurator](#)
- [Distribution Home](#)
- [Contractor Connection](#)
- [ez-Learn](#)
- [ez-Find](#)
- [Sign In - B2B](#)
- [OEM Home](#)
- [How to Buy](#)
- [Whats New](#)
- [Press/News](#)
- [Retail Home](#)
- [Product Information](#)
- [How To](#)
- [Merchandising](#)
- [Energy Smart Living](#)
- [International Home](#)
- [China \(English\)](#)
- [China \(Chinese\)](#)
- [Mexico \(English\)](#)
- [Mexico \(Spanish\)](#)
- [Middle East \(English\)](#)
- [International Contact](#)
- [Press](#)
- [Products](#)
- [Trade Shows](#)
- [Made to Order](#)
- [EZE-Rough](#)
- [Acenti Devices](#)
- [AC Switches](#)
- [Appliance Switches](#)
- [Architectural Controls](#)
- [Camera Systems](#)
- [Combination Devices](#)
- [Connectors & Cables](#)
- [Cord Sets](#)
- [Corrosion Resistant Devices](#)
- [Daylighting Controls](#)
- [Decora Devices](#)
- [Dimmers](#)
- [Cam-Type Devices](#)
- [Electrical Accessories](#)
- [Entertainment Accessories](#)
- [Entertainment Fixtures](#)
- [Entertainment Lighting Controls](#)
- [Entertainment Lighting Kits](#)

- [Electrical](#)
- [Network Solutions](#)
- [Lighting Controls](#)
- [Entertainment](#)
- [Home Automation](#)
- [Connected Home](#)
- [Energy Management](#)
- [Power Quality](#)



66591-6C

Description

15 Amp, 125 Volt, NEMA 5-15, 6 FT. Cord Set, Straight Blade, Industrial Grade, Automatic Reset GFCI Devices, 14-3-SJT-Yellow Cord

Product Features

- Grounding: GFCI Ground Fault
- Feature: Automatic Reset GFCI
- Amperage: 15 Amp
- Voltage: 125 Volt
- NEMA: 5-15
- Pole: 2
- Wire: 3
- Cord Length: 6 FT.
- Cord Type: 14-3-SJT-Yellow
- Body Material: Moulded Vinyl
- Blades/Contacts: Brass
- Assembly Screws: N/A
- Color: Yellow-Black
- Standards and Certifications: UL/CSA
- Warranty: 1-Year Limited

[ZOOM](#)

Quantity: