

Solutions for Electronic Specialty Markets (ESM)


Product Catalog for Electronic Specialty Markets

- 3M™ Electronic Specialty Markets New Product Releases
- 3M™ Abrasives
- 3M™ Adhesives, Cleaners & Compounds
- 3M™ Breadboards & Test Clips
- 3M™ Cable & Assemblies
- 3M™ Copper Interconnects
- 3M™ Fiber Optics
- 3M™ Fire Protection
- 3M™ Heat Shrink
- 3M™ Identification Systems
- 3M™ Occupational Health & Safety Products
- 3M™ Protective Bumpers
- 3M™ Reclosable Fasteners
- 3M™ Splicing, Terminating & Ducting
- 3M™ Static Control
- 3M™ Tapes
- 3M™ Terminals, Kits & Tools
- 3M™ Vacuums & Accessories
- 3M™ Warehousing & Packaging Supplies
- 3M™ Wire Connectors

[Product Catalog for Electronic Specialty Markets](#) [3M™ Terminals, Kits & Tools](#) [Forks](#)
[Scotchlok™ Locking Fork Terminals](#) - [Vinyl Insulated Brazed Seam](#)

3M™ Scotchlok™ Vinyl Insulated Brazed Seam Locking Fork Terminal MV10 -6FLK, Stud Size 6

[Printer-friendly format](#)



This terminal has a wire range of 12 - 10 AWG and a stud size of 6. It comes in case quantities of 500 per case.

[\[click to enlarge\]](#)

GTIN(UPC/EAN) : 0 00 54007 13949 2
 3M Id : 80 - 6101 - 3423 - 3

Additional Information

The spring - like tongue locks into place around the stud even when the mount screw is not tightened. Extra force is required to remove it from the stud.

Learn More . . .

- [Packaging Data](#)
- [Locking Forks - Vinyl Insulated Brazed Seam 12 - 10 AWG - Product Selection Guide \(PDF 23.7 K\)](#)
- [Scotchlok Terminals MV18 - 4FL thru MV10 - 14FL - Data Sheet \(PDF 19.6 K\)](#)
- [Terminal Stud Size Chart - Product Selection Guide \(PDF 5.2 K\)](#)

Please Note:

Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Agency Approvals	UL and CSA
Barrel Style	Brazed
China RoHS - Below MCV	No
CSA File Number	LR22190
EPC Can View	Public
EU RoHS Compliant	No
Insulation Material	Vinyl
Stud Size	6 American Wire Gauge (AWG)
Terminal Style	Locking
Terminal Type	Fork
UL File Number	E23438
Wire Gauge Range	10 to 12 American Wire Gauge (AWG)

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Search This Product Catalog

By Keyword ▼