

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0022057115**  
**Status:** **Contact Molex**  
**Description:** 2.50mm (.098") Pitch SPOX™ Wire-to-Board Header, Right Angle, Shrouded, Friction Lock, 11 Circuits

**Documents:**

3D Model  
Drawing (PDF)  
Product Specification PS-5264-001 (PDF)

Packaging Specification SPK-5268-001 (PDF)  
RoHS Certificate of Compliance (PDF)

**Agency Certification**

CSA LR19980  
UL E29179

**General**


Product Family PCB Headers  
Series 5268  
Application Signal, Wire-to-Board  
Product Name SPOX™

**Physical**

Breakaway No  
Circuits (Loaded) 11  
Circuits (maximum) 11  
Color - Resin Natural  
Durability (mating cycles max) 30  
First Mate / Last Break No  
Flammability 94V-0  
Glow-Wire Compliant No  
Guide to Mating Part No  
Keying to Mating Part None  
Lock to Mating Part Yes  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Material - Resin Nylon  
Number of Rows 1  
Orientation Right Angle  
PC Tail Length 3.50mm (.138")  
PCB Locator No  
PCB Retention None  
PCB Thickness - Recommended 1.60mm (.063")  
Packaging Type Bag  
Pitch - Mating Interface 2.50mm (.098")  
Plating min - Mating 4.064µm (160µ")  
Plating min - Termination 4.064µm (160µ")  
Polarized to Mating Part Yes  
Polarized to PCB No  
Shrouded Fully  
Stackable No  
Surface Mount Compatible (SMC) No  
Temperature Range - Operating -40°C to +105°C  
Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 3A  
Voltage - Maximum 250V



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

5268Series

**Mates With**

5264 SPOX™ Wire-to-Board Crimp Housing

**Material Info**

Old Part Number

5268-11A

**Reference - Drawing Numbers**

Packaging Specification

SPK-5268-001

Product Specification

PS-5264-001, RPS-5264-005, RPS-5268-001

Sales Drawing

SD-5268-NA

This document was generated on 05/13/2011

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**