

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0395338004](#)
Status: **Active**
Overview: Eurostyle Terminal Blocks
Description: 5.08mm Pitch Eurostyle Vertical Plug, Front Wire Entry, Green Housing, 4 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-39500-001-001 \(PDF\)](#)

General

| | |
|----------------|---|
| Product Family | Terminal Blocks |
| Series | 39533 |
| Application | N/A |
| Comments | Front Wire Entry |
| Component Type | Plug |
| Overview | Eurostyle Terminal Blocks |
| Product Name | ESE, Eurostyle Pluggable |
| Type | Euro Block |
| UPC | 822350533997 |

Physical

| | |
|-------------------------------|--------------------------------|
| Circuits (Loaded) | 4 |
| Entry Angle | Horizontal |
| Lock to Mating Part | Yes |
| Number of Rows | 1 |
| Orientation | Vertical |
| Panel Mount | No |
| Pitch - Mating Interface | 5.08mm |
| Pitch - Termination Interface | 5.08mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | 12, 14, 16, 18, 20, 22, 24, 26 |
| Wire Size mm ² | 0.13-3.31 |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 18.0A |
| Voltage - Maximum | 300V |


Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|------------------|
| Product Specification | PS-39500-001-001 |
| Sales Drawing | SD-39533-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[39533 Series](#)

Mates With

[39531](#) Vertical PCB Header, [39532](#) Horizontal PCB Header, Most 5.08mm Pitch Industry Standard PCB Headers, [39538](#) Dual Level Header, Open Ends