

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0428171034](#)
Status: **Active**
Overview: [Mini-Fit Sr. Power Connectors](#)
Description: [Mini-Fit Sr. Crimp Terminal, Male, 8 AWG, Silver \(Ag\)](#)

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-42815-004-001 \(PDF\)](#)
[Product Specification PS-42815-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-42815-001-001 \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [42817](#)
Application [Power, Wire-to-Wire](#)
Comments [High Current/Low Force
See Product Specification for maximum current rating by circuit size and application.](#)
Crimp Quality Equipment [Yes](#)
Overview [Mini-Fit Sr. Power Connectors](#)
Product Name [Mini-Fit Sr.](#)
UPC [889056244756](#)

Physical

Gender [Male](#)
Material - Metal [High Performance Alloy \(HPA\)](#)
Material - Plating Mating [Silver](#)
Material - Plating Termination [Tin](#)
Net Weight [1.389/g](#)
Packaging Type [Reel](#)
Plating min - Mating [2.540µm](#)
Plating min - Termination [2.540µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [6.60mm max.](#)
Wire Size AWG [12+12, 8](#)
Wire Size mm² [N/A](#)

Electrical

Current - Maximum per Contact [50.0A](#)


Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Reference - Drawing Numbers

Application Specification [AS-42815-001-001](#)
Product Specification [PS-42815-001-001](#)
Test Summary [TS-42815-004-001](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42817 Series](#)

Use With

Mini-Fit Sr. Plug Housings [42818](#) , [43938](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 10.00mm Pitch Mini-Fit Sr. Crimp Terminals, 8 AWG	2002188700
Extraction Tool for Mini-Fit Sr. Terminals, 8-16 AWG	638130400
Mini-Mac Applicator	638911000
Mini-Mac Applicator for Terminals	638919500

This document was generated on 05/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION