

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0436450208](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: [Micro-Fit 3.0 Receptacle Housing, Single Row, 2 Circuits, UL 94V-0, Low-Halogen Since Inception, Black](#)

Documents:

| | |
|--|--|
| Drawing (PDF) | Test Summary TS-43045-001-001 (PDF) |
| 3D Model | Test Summary TS-43045-002-001 (PDF) |
| Product Specification PS-43650 (PDF) | Test Summary TS-46235-001-001 (PDF) |
| Application Specification 430250000-AS-000 (PDF) | RoHS Certificate of Compliance (PDF) |
| Packaging Specification PK-43645-001-001 (PDF) | Product Literature (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|-----------------------------|--|
| Product Family | Crimp Housings |
| Series | 43645 |
| 3D Viewer | Yes |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Comments | Halogen Free/Low Halogen since inception, Halogen Free/Low Halogen since inception |
| Overview | Micro-Fit Connector System |
| Product Literature Order No | 987650-5984 |
| Product Name | Micro-Fit 3.0 |
| UPC | 883906111304 |

Physical

| | |
|-------------------------------|----------------|
| Circuits (maximum) | 2 |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 0.272/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.00mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |


Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|------------------|
| Application Specification | 430250000-AS-000 |
| Packaging Specification | PK-43645-001-001 |
| Product Specification | PS-43650 |
| Sales Drawing | SD-43645-001-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43645 Series](#)

Mates With

Micro-Fit 3.0 Plug Housings [43640](#)

Micro-Fit* TPA Plug Housing [200875](#)

Micro-Fit 3.0 Headers [43650](#)

Use With

Micro-Fit 3.0 Female Crimp Terminals [43030](#), [45773](#), Micro-Fit RMF Female Crimp Terminals [46235](#)

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION