

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0441500013**
Status: **Active**
Overview: Magnetic and Modular Jacks/Plugs
Description: Modular Jack, Right-Angle, Low Profile, 8/8, 6 Ports

Documents:

3D Model	Packaging Specification PK-44150-004-000 (PDF)
Drawing (PDF)	Test Summary TS-44050-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-44050-003 (PDF)	

Agency Certification

CSA	LR19980
UL	E107635

General


Product Family	Modular Jacks/Plugs
Series	<u>44150</u>
Comments	External Shield, External Shield
Component Type	PCB Jack
Magnetic	No
Overview	<u>Magnetic and Modular Jacks/Plugs</u>
Performance Category	5, 5e
Power over Ethernet (PoE)	N/A
Product Name	Modular Jack 8/8, RJ45
UPC	800754812825

Physical

Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Inverted / Top Latch	No
Jack Height	13.31mm
Lightpipes/LEDs	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	25.110/g
Orientation	Right Angle (Side Entry)
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	1.270µm
Plating min - Termination	2.540µm
Port Configuration	1x6
Positions / Loaded Contacts	8/8
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	150V AC (RMS)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[44150 Series](#)

Mates With

FCC 68 Plugs

Solder Process Data

Lead-freeProcess Capability

WAVE

Material Info**Reference - Drawing Numbers**

Packaging Specification

PK-44150-004-000

Product Specification

PS-44050-003

Sales Drawing

SD-44150-002-001

Test Summary

TS-44050-001-001

This document was generated on 12/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION