

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0988251061](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: NSCC, Pin Connector Hybrid, Unsealed, 6 Circuits, Black

Documents:

3D Model	Application Specification AS-98821-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-98825-001 (PDF)
Product Specification PS-98821-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	98825
Application	Power, Wire-to-Wire
Application Tooling Part Link	63813-3800
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348817283

Physical

Circuits (maximum)	6
Circuits Detail	4 x 1.5 + 2 x 2.8
Color - Resin	Black
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	8.435/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.33mm, 4.20mm, 5.00mm
Pitch - Termination Interface	3.33mm, 4.20mm, 5.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +85°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	08311EV6F1
--------------------	------------

Reference - Drawing Numbers

Application Specification	AS-98821-001-001
Packaging Specification	PK-98825-001
Product Specification	PS-98821-001-001
Sales Drawing	SD-98825-002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[98825](#) Series

Mates With

[98821-1061](#)

Use With

Use with FCI Male Terminals

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extractor Tool for Unsealed Receptacle Connectors	0638133800

This document was generated on 08/03/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION