

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2004530002](#)  
**Status:** **Active**  
**Overview:** Mini-Fit Jr. Power Connectors  
**Description:** Mini-Fit TPA2 Receptacle Housing, 4.20mm Pitch, Single Row, UL 94V-0, Low-Halogen, 2 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 2004530000-PK-000 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Test Summary 1727180001-TS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 1727180002-TS-000 (PDF)</a>
<a href="#">Product Specification PS-172718-0000-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-172718-0000-001 (PDF)</a>	

**Agency Certification**

UL EU-01109

**General**

Product Family	Crimp Housings
Series	<a href="#">200453</a>
3D Viewer	Yes
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See product specification for current derating information., See product specification for current derating information.
Overview	<a href="#">Mini-Fit Jr. Power Connectors</a>
Product Name	Mini-Fit TPA2
UPC	889056445658


**Physical**

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.700/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-172718-0000-001
Packaging Specification	2004530000-PK-000
Product Specification	PS-172718-0000-001
Sales Drawing	2004530000-SD-000
Test Summary	1727180001-TS-000, 1727180002-TS-000



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[200453](#) Series

**Mates With**

Mini-Fit TPA2 Plug Housing [200471](#) ,  
[200488](#) <br>Mini-Fit Jr. Plug Housing [5559](#)  
 <br>Mini-Fit Jr. Headers [5566](#) , [5569](#)

**Use With**

Mini-Fit TPA2 Female Terminal [172718](#)  
 <br>Mini-Fit TPA2 Retainer [172709](#)  
 <br>Mini-Fit TPA2 CPA Retainer [203603](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**