

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5024262630**  
**Status:** **Active**  
**Overview:** SlimStack™ 0.40mm Pitch Board-to-Board Connectors  
**Description:** 0.40mm Pitch SlimStack™ Board-to-Board Receptacle, Surface Mount, Dual Row, Vertical, 1.00mm Stacking Height, with Solder Tabs, with Vacuum Tape, 26 Circuits

**Documents:**

[3D Model](#) [Packaging Specification SPK-502426-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Application Specification AS-502426-001-001 \(PDF\)](#)

**General**

Product Family PCB Receptacles  
Series [502426](#)  
Application Board-to-Board, Signal  
Overview [SlimStack™ 0.40mm Pitch Board-to-Board Connectors](#)  
Product Name SlimStack™  
UPC 800756832296

**Physical**

Circuits (Loaded) 26  
Circuits (maximum) 26  
Color - Resin Black  
Durability (mating cycles max) 30  
Glow-Wire Compliant No  
Lock to Mating Part Yes  
Mated Height 1.00mm  
Material - Metal Phosphor Bronze  
Material - Plating Mating Gold  
Material - Plating Termination Gold  
Net Weight 29.559/mg  
Number of Rows 2  
Orientation Vertical  
PCB Locator No  
PCB Retention Yes  
Packaging Type Embossed Tape on Reel  
Pitch - Mating Interface 0.40mm  
Polarized to Mating Part No  
Polarized to PCB No  
Stackable No  
Temperature Range - Operating -25°C to +85°C  
Termination Interface: Style Surface Mount


**Electrical**

Current - Maximum per Contact 0.3A  
Voltage - Maximum 50V AC/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification AS-502426-001-001  
Packaging Specification SPK-502426-001-001  
Sales Drawing SD-502426-003, SD-502426-004



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Green Image  
ELV Not Relevant  
RoHS Phthalates Not Contained

**Search Parts in this Series**

[502426](#) Series

**Mates With**

[502430](#) PCB Header