

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009508060

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, 6 Circuits

Documents:

3D Model

Packaging Specification PK-41695-001-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-08-50-001 (PDF)

|                               |                                 |
|-------------------------------|---------------------------------|
| Agency Certification          |                                 |
| CSA                           | LR19980                         |
| UL                            | E29179                          |
| General                       |                                 |
| Product Family                | Crimp Housings                  |
| Series                        | 41695                           |
| Application                   | Power, Wire-to-Board            |
| Overview                      | KK® Interconnect System - Molex |
| Product Name                  | KK® 396                         |
| UPC                           | 800754227735                    |
| Physical                      |                                 |
| Breakaway                     | No                              |
| Circuits (maximum)            | 6                               |
| Color - Resin                 | Natural                         |
| Flammability                  | 94V-0                           |
| Gender                        | Receptacle                      |
| Glow-Wire Compliant           | No                              |
| Keying to Mating Part         | None                            |
| Lock to Mating Part           | None                            |
| Material - Resin              | Polyester                       |
| Net Weight                    | 2.001/g                         |
| Number of Rows                | 1                               |
| Packaging Type                | Bag                             |
| Panel Mount                   | No                              |
| Pitch - Mating Interface      | 3.96mm                          |
| Temperature Range - Operating | See Product Specification       |
| Solder Process Data           |                                 |
| Lead-freeProcess Capability   | N/A                             |
| Material Info                 |                                 |
| Engineering Number            | 41695NA06                       |
| Reference - Drawing Numbers   |                                 |
| Packaging Specification       | PK-41695-001-001                |
| Product Specification         | PS-08-50-001                    |
| Sales Drawing                 | SD-41695                        |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/30/2017 (7 July

2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

41695 Series

Mates With

KK® 396 Header [41791](#) , [41792](#) , [41671](#) , [41672](#) , [41661](#) , [41662](#)

Use With

KK® 396 Crimp Terminals, [2478](#) , [2578](#) , [6838](#) , [7258](#) , [45570](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION