


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0345760703**
Status: **Active**
Overview: MX123™ Sealed Connection System
Description: 2.54mm Pitch, MX123™ Female Receptacle Housing, Keying Option G, Wire Dress Option 0, 56 Circuits, Blue TPA

Documents:

3D Model	Product Specification TS-34566-1546-001 (PDF)
Drawing (PDF)	Application Specification AS-34566-001-001 (PDF)
Product Specification PS-34566-0000-001 (PDF)	Packaging Specification PK-31300-019 (PDF)
Product Specification TS-34566-002-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	34576
Application	Power, Wire-to-Board
Comments	See Sales Drawing for number of Open Circuits
Overview	<u>MX123™ Sealed Connection System</u>
Product Name	MX123
UPC	822348356713

Physical

Circuits (maximum)	56
Circuits Detail	56
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	41.804/g
Number of Rows	4
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	11.0A, 25.0A
-------------------------------	--------------

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34566-001-001
Packaging Specification	PK-31300-019
Product Specification	PS-34566-0000-001, TS-34566-002-001, TS-34566-1546-001
Sales Drawing	12642694-001, 12672832-001, SD-34576-0001, SD-34576-001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34576 Series](#)

Mates With

MX123™ Header [31386](#) , [31387](#)

Use With

MX64™ Female Terminals [33467](#) (AWG, Gold)
MX64™ Female Terminals [34736](#) (AWG, Silver)
MX64™ Female Terminals [34736](#) (ISO, Silver)

This document was generated on 08/23/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION