

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0460123242
Status: Active
Overview: Mini-Fit Plus Connector System
Description: Mini-Fit® Plus Crimp Terminal, 16 AWG, Bag, Selective Gold (Au) Plating 0.76µm

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-45750-001-001 \(PDF\)](#)
[Packaging Specification PK-5556-003 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	46012
Application	Power
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current de-rating information.
Crimp Quality Equipment	Yes
Overview	Mini-Fit Plus Connector System
Packaging Alternative	46012-3241 (Reel)
Product Name	Mini-Fit® Plus
UPC	822350570503
Physical	
Durability (mating cycles max)	250
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.144/g
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.20-3.15mm
Wire Size AWG	16
Wire Size mm²	N/A

Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers	
Packaging Specification	PK-5556-003
Product Specification	PS-45750-001-001
Sales Drawing	SD-46012-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/30/2017 (7 July 2017) Halogen-Free Status Low-Halogen	China RoHS
---	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
46012 Series

Mates With
45750 Mini-Fit® Plus Crimp Terminal

Use With
5559 Mini-Fit Jr.™ Plugs, 42475 Mini-Fit® MBI Panel Mount Plugs, 30068 Mini-Fit® TPA Plugs