

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5051100792](#)
Status: **Active**
Overview: [FFC-FPC \(SMT\)](#)
Description: 0.50mm Pitch Easy-On™ Type FFC/FPC Connector, 1.90mm Height, Double Bottom Contact Type (FD19 Series), Right Angle, Surface Mount, ZIF, 7 Circuits

Documents:

[3D Model](#) [Packaging Specification 5051109200-201 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 5051100002-000 \(PDF\)](#)

General

Product Family FFC/FPC Connectors
 Series [505110](#)
 Comments Black Actuator
 Overview [FFC-FPC \(SMT\)](#)
 Product Name Easy-On™
 UPC 889056255813

Physical

Circuits (Loaded) 7
 Circuits (maximum) 7
 Color - Resin Beige
 Contact Position Bottom
 Durability (mating cycles max) 25
 Entry Angle 90° Angle
 Mated Height 1.90mm
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold over Nickel
 Material - Plating Termination Gold over Nickel
 Material - Resin Liquid Crystal Polymer
 Net Weight 92.500/mg
 Number of Rows 1
 Orientation Right Angle
 PCB Locator No
 PCB Retention Yes
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 0.50mm
 Pitch - Termination Interface 0.50mm
 Plating min - Mating 0.051µm
 Plating min - Termination 0.051µm
 Polarized to PCB Yes
 Stackable No
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Surface Mount
 Wire/Cable Type FFC/FPC


Electrical

Current - Maximum per Contact 0.5A
 Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Package Specification [5051109200-201](#)
 Product Specification [5051100002-000](#)
 Sales Drawing [5051100001-000](#), [5051101001-000](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[505110](#) Series

This document was generated on 06/15/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION