

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0330123021

Status:

Active

Overview:

MX150™ Unsealed Connector System

Description:

MX150™ Female Terminal, Tin Plating, 14 and 16 AWG, Left Reel Payoff, Use with MX150 Unsealed Connectors. Not suitable for MX150 Sealed Connectors.



Series image - Reference only

Documents:	
Drawing (PDF)	Application Specification AS-33012-002-CH-001 (PDF)
Product Specification PS-33012-002-001 (PDF)	Application Specification AS-33012-002-FR-001 (PDF)
Product Specification TS-33012-002-001 (PDF)	Packaging Specification 313025040-000 (PDF)
Application Specification AS-33012-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	33012
Application	Power
Comments	Left Reel Payoff, Large Polarization Rib. Not to be used with MX150 Sealed Connectors
Crimp Quality Equipment	Yes
Overview	MX150™ Unsealed Connector System
Product Name	MX150™
UPC	822350084413
Physical	
Gender	Female
Grip Code	14
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.434/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	14, 16
Wire Size mm²	1.50
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-33012-002-001, AS-33012-002-CH-001, AS-33012-002-FR-001
Packaging Specification	313025040-000
Product Specification	PS-33012-002-001, TS-33012-002-001
Sales Drawing	SD-33012-002

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC
Not Contained Per
-ED/01/2017 (12
January 2017)
Halogen-Free
Status
Not Relevant

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV
RoHS Phthalates

Not Relevant
Compliant
Not Contained

Search Parts in this Series
33012 Series

Use With
33472 Dual Row Housing, 33476 Hybrid
Housing, 33471 Single Row Housing

This document was generated on 08/23/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION