


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0510901300**  
**Status:** **Active**  
**Description:** 2.00mm Pitch Mi II™ System Wire-to-Board Crimp Housing, Single Row, 13 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51090-016-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51090-017-001 (PDF)</a>
<a href="#">Product Specification PS-51090-003 (PDF)</a>	<a href="#">Product Specification PS-53358-001-001 (PDF)</a>
<a href="#">Product Specification PS-51090-004-001 (PDF)</a>	<a href="#">Application Specification 510900001-000 (PDF)</a>
<a href="#">Product Specification PS-51090-005-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-51090-009 (PDF)</a>	



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	51090
Application	Signal, Wire-to-Board
Product Name	Mi II™
UPC	800753688247

**Physical**

Circuits (maximum)	13
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	438.500/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	510900001-000
Product Specification	PS-51090-003, PS-51090-004-001, PS-51090-005-001, PS-51090-009, PS-51090-016-001, PS-51090-017-001, PS-53358-001-001
Sales Drawing	SD-51090-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[51090 Series](#)

**Mates With**

[55460](#) , [53324](#) , [53325](#)

**Use With**

[50212 Crimp Terminals](#)