


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0593708100**
Status: **Active**
Description: 2.00mm Pitch Crimp Terminal, Female, 22-28 AWG, For 51216, Bag

Documents:

3D Model	Product Specification PS-51353-010-001 (PDF)
Drawing (PDF)	Application Specification 5055960000-AS-000 (PDF)
Product Specification 5055960000-000 (PDF)	Application Specification 5055960000-AS-001 (PDF)
Product Specification 5055960000-PS-000 (PDF)	Application Specification 5055960001-000 (PDF)
Product Specification PS-51216-005-001 (PDF)	Application Specification 5055960001-001 (PDF)
Product Specification PS-51216-006-001 (PDF)	Packaging Specification SPK-59370-001-001 (PDF)
Product Specification PS-51216-007-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	<u>59370</u>
Application	Signal
Crimp Quality Equipment	Yes
Packaging Alternative	<u>59370-8000</u> (Reel)
Product Name	N/A
UPC	800754824330

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	61.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.50mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Application Specification	5055960000-AS-000, 5055960000-AS-001, 5055960001-000, 5055960001-001
Packaging Specification	SPK-59370-001-001
Product Specification	5055960000-000, 5055960000-PS-000, PS-51216-005-001, PS-51216-006-001, PS-51216-007-001, PS-51353-010-001
Sales Drawing	SD-59370-004

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

59370 Series

Use With

51216