


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349610340](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50™ Unsealed Right Angle Hybrid Header, 3 Rows, 34 Circuit, Polarization Option A, Black, Tray

Documents:

3D Model	Packaging Specification PK-31302-070 (PDF)
Drawing (PDF)	Test Summary TS-34961-001 (PDF)
Product Specification PS-34959-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34959-001-001 (PDF)	Product Literature (PDF)



General

Product Family	PCB Headers
Series	34961
Application	Power, Signal, Wire-to-Board
Comments	0.50mm blades = 4.0A; 1.20mm blades = 16.0A
Overview	Mini50 Connection Systems
Product Literature Order No	987650-5442
Product Name	Mini50™
UPC	887191703725

Physical

Breakaway	No
Circuits (Loaded)	34
Circuits (maximum)	34
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	SPS
Net Weight	12.964/g
Number of Rows	3
Orientation	Right Angle
PC Tail Length	2.75mm
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	16.0A, 4.0A
Voltage - Maximum	500V DC

Material Info

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34961](#) Series

Mates With

Mini50™ Unsealed 3 Row Receptacle
[34959](#)

Reference - Drawing Numbers

Application Specification	AS-34959-001-001
Packaging Specification	PK-31302-070
Product Specification	PS-34959-001-001
Sales Drawing	SD-34961-030
Test Summary	TS-34961-001

This document was generated on 08/22/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION