

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5037640301](#)  
**Status:** **Active**  
**Overview:** [Pico-Lock Connector System](#)  
**Description:** 1.00mm Pitch, Pico-Lock Receptacle Crimp Housing, Single Row, Positive Lock, 3 Circuits, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-503764-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification SPK-503764-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 5037641001-PS-000 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Product Specification PS-503764-001-001 (PDF)</a>	

**Agency Certification**

UL E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">503764</a>
Application	Signal, Wire-to-Board
Comments	See Molex product specification PS-503764-001 for additional current de-rating information
Overview	<a href="#">Pico-Lock Connector System</a>
Product Name	Pico-Lock
UPC	191128847070


**Physical**

Circuits (maximum)	3
Color - Resin	Black
Flammability	SC-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Net Weight	23.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-503764-001-001
Packaging Specification	SPK-503764-001-001
Product Specification	5037641001-PS-000, PS-503764-001-001
Sales Drawing	5037640000-SD-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[503764](#) Series

**Mates With**

[503763](#) Pico-Lock Wire-to-Board Header

**Use With**

[503765](#) Pico-Lock Crimp Terminal