


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [09-52-4134](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: 3.96mm Pitch KK® Crimp Housing, Female, Friction Ramp, 13 Circuits

Documents:

| | |
|---|---|
| 3D Model | Product Specification PS-5239-007 (PDF) |
| Drawing (PDF) | Product Specification PS-5239-010 (PDF) |
| Product Specification PS-5239-002 (PDF) | Product Specification PS-5239-011 (PDF) |
| Product Specification PS-5239-003 (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-5239-006 (PDF) | |



General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 5239 |
| Application | Power, Wire-to-Board |
| Overview | KK® Interconnect System - Molex |
| Product Name | KK® |
| UPC | 800753692664 |

Physical

| | |
|-------------------------------|-----------------|
| Circuits (maximum) | 13 |
| Color - Resin | Natural |
| Gender | Female |
| Glow-Wire Compliant | No |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 3301.000/mg |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.96mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |

Material Info

Old Part Number 5239-13

Reference - Drawing Numbers

| | |
|-----------------------|--|
| Product Specification | PS-5239-002, PS-5239-003, PS-5239-006, PS-5239-007, PS-5239-010, PS-5239-011, RPS-5239-001 |
| Sales Drawing | SD-5239-N |

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5239Series](#)

Mates With

Right Angle PCB Header, [5274](#) [5272](#) ,
 Vertical PCB Header [5271](#) , [5273](#)

Use With

[5168](#) Cat Ear Crimp Terminals for 22-28 AWG, [5167](#) Cat Ear Crimp Terminals for 18-24 AWG, [2478](#) Crimp Terminal, [2578](#) Crimp Terminal