

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0357470410

Status:


Active

Overview:

VersaBlade™ Wire-to-Wire Connector System

Description:

VersaBlade™ .070 Male Crimp Terminal, 24 AWG, Type B



Series image - Reference only

Documents:	
3D Model	Product Specification PS-35180-003 (PDF)
Drawing (PDF)	Packaging Specification PK-35747-001 (PDF)
Product Specification PS-35150-003 (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	Crimp Terminals
Series	35745
Application	Power
Crimp Quality Equipment	Yes
Overview	VersaBlade™ Wire-to-Wire Connector System
Product Name	VersaBlade™
UPC	822348431038
Physical	
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.352/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.20mm max.
Wire Size AWG	24, 26
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-35747-001
Product Specification	PS-35150-003, PS-35180-003, RPS-35180-001
Sales Drawing	SD-35747-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

35745 Series

Mates With

35748 Crimp Terminal

Use With

35150 VersaBlade™ Hybrid Receptacle
Housing. 35151 VersaBlade™ Hybrid Plug
Housing

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description

FineAdjust™
Applicator for .070

Product #

0639020700

Female Crimp
Terminal.
Hand Crimp Tool for [0638196800](#)
Industry standard
1.78mm Terminals
Extraction Tool [0638132700](#)
Hand Crimp Tool for [0638196900](#)
Industry standard
1.78mm Tab
Terminals, 24-26
AWG Wire
T2 Terminator [0639120700](#)
for .070 Female
Crimp Terminal

This document was generated on 04/01/2016
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION