

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0561349100**  
**Status:** **Active**  
**Overview:** MicroClasp™ Wire-to-Board System  
**Description:** 2.00mm Pitch Crimp Terminal, Female, 22-28 AWG, Copper Alloy, Bag

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51353-012-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51382-004-001 (PDF)</a>
<a href="#">Product Specification 5055960000-PS-000 (PDF)</a>	<a href="#">Application Specification 5055960000-AS-000 (PDF)</a>
<a href="#">Product Specification PS-500637-001-001 (PDF)</a>	<a href="#">Application Specification 5055960000-AS-001 (PDF)</a>
<a href="#">Product Specification PS-500730-001-001 (PDF)</a>	<a href="#">Packaging Specification SPK-56134-001-001 (PDF)</a>
<a href="#">Product Specification PS-51242-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-51353-003-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	<u>56134</u>
Application	Signal
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	<u>MicroClasp™ Wire-to-Board System</u>
Packaging Alternative	<u>56134-9000 (Reel)</u>
Product Name	MicroClasp™
UPC	756054317778


**Physical**

Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	36.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.70mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

**Material Info**

**Reference - Drawing Numbers**

Application Specification	5055960000-AS-000, 5055960000-AS-001
Packaging Specification	SPK-56134-001-001
Product Specification	5055960000-PS-000, PS-500637-001-001, PS-500730-001-001, PS-51242-002-001, PS-51353-003-001, PS-51353-012-001, PS-51382-004-001
Sales Drawing	SD-56134-005



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

56134 Series

**Use With**

Housings 500915 , 51242 , 51353, 51382,  
505596