
Part Number : 2037025000
Product Description : FineAdjust Applicator for Mega-Fit Male and Female Crimp Terminals, 16 AWG (UL 1007 / UL 1061) Wire
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules



Documents & Resources

Tooling Specifications

2037025000-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Mega-Fit Male and Female Crimp Terminals, 16 AWG (UL 1007 / UL 1061) Wire
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust,Mega-Fit
Tool Type	Applicator
UPC	196823302275
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	1.000/g

Applicable Parts

Description	Part Number
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, Double 16+16 or Single 12 AWG, Reel	768230343
Mega-Fit Crimp Terminal, Male, Tin (Sn) Plating, Double 16+16 or Single 12 AWG, Reel	1054170333
Mega-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	1054180313
Mega-Fit Crimp Terminal, Male, 0.76µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	1054181313
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	1720630333
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	1720631333