




Part Number : [2160111042](#)
Product Description : Super Sabre-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 4 Circuits, Black
Series Number : 216011
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

- Drawings**
[2160111042 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	216011
Description	Super Sabre-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 4 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Super Sabre-to-Pigtail
Product Name	Super Sabre
Type	Discrete Wire Assembly
UPC	193264830589

Electrical

Current - Maximum per Contact	34.0A
Voltage - Maximum	600V AC/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper
Material - Plating Mating	Silver

Material - Plating Termination	Matte Tin, Nickel
Material - Resin	Nylon
Net Weight	77.750/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	7.50mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	10

Mates With / Use With

Mates with Part(s)

Description	Part Number
Super Sabre Vertical Headers	<u>172042</u>
Super Sabre Right-Angle Headers	<u>172043</u>
Super Sabre Single Row Plug Housings	<u>172673</u>
Sabre Plug Crimp Housings	<u>43680</u>