




Part Number : [2069972201](#)
Product Description : CP-4.5 Plug Housing, 4.50mm Pitch, Dual Row, 2 Circuits, Blue, Glow-Wire Capable
Series Number : 206997
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

[2069972201_sd.pdf](#)
[2069960000PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2069960000PK-000.pdf](#)
[2069960000PS-002.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	206997
Description	CP-4.5 Plug Housing, 4.50mm Pitch, Dual Row, 2 Circuits, Blue, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	CP-4.5
UPC	193264462032

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	2
Color - Resin	Blue
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon

Net Weight	1.250/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.50mm
Pitch - Termination Interface	4.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
CP-4.5 Receptacle Housing, 4.50mm Pitch, Dual Row, Polarized, Positive Lock, 2 Circuits, Blue, Glow-Wire Capable	<u>2069962201</u>

Use with Part(s)

Description	Part Number
CP-4.5 Wire-to-Wire Genderless Crimp Terminal, Pre-Tin Plating, 20-16 AWG, Reel	<u>2069998000</u>
CP-4.5 Wire-to-Wire Genderless Crimp Terminal, Pre-Tin Plating, 26-22 AWG, Reel	<u>2070008000</u>
CP-4.5 Terminal Position Assurance (TPA) Retainer, 2 Circuits, Gray	<u>2069980100</u>