



Part Number : [2122132030](#)
Product Description : CP-3.3 Terminal Position Assurance (TPA) Retainer, 3 Circuit
Series Number : 212213
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[2122132030_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2122139200-SPK-200.pdf](#)
[2122090000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	212213
Description	CP-3.3 Terminal Position Assurance (TPA) Retainer, 3 Circuit
Component Type	Terminal Position Assurance
Product Name	CP-3.3
UPC	193264100095

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Brown
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	84.230/mg
Number of Rows	1
Packaging Type	Bag

Mates With / Use With

Use with Part(s)

Description	Part Number
CP-3.3 Receptacle Housing, 3.30mm Pitch, Dual Row, Positive Lock, Glow-Wire Capable, 6 Circuits, Natural	<u>2122092060</u>
CP-3.3 Receptacle Housing, 3.30mm Pitch, Dual Row, Positive Lock, Glow-Wire Capable, 6 Circuits, Black	<u>2122092061</u>
CP-3.3 Receptacle Housing, 3.30mm Pitch, Dual Row, Positive Lock, Glow-Wire Capable, 6 Circuits, Red	<u>2122092062</u>
CP-3.3 Receptacle Housing, 3.30mm Pitch, Dual Row, Positive Lock, Glow-Wire Capable, 6 Circuits, Yellow	<u>2122092063</u>