




Part Number : [2137201000](#)
Product Description : Micro-Lock Plus Male Crimp Terminal, 2.00mm Pitch, Matte Tin (Sn) Plating, 26-22 AWG, Reel
Series Number : 213720
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings

[2137201000_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[5055700001-A03.pdf](#)

[2137209200-SPK-200.pdf](#)

[5055700003-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	213720
Description	Micro-Lock Plus Male Crimp Terminal, 2.00mm Pitch, Matte Tin (Sn) Plating, 26-22 AWG, Reel
Application	Power, Wire-to-Wire
Product Name	Micro-Lock Plus
UPC	193264756582

Physical

Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	62.910/mg
Packaging Type	Reel
Plating min - Mating	0.700µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.50mm
Wire Size (AWG)	22, 24, 26
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
2.00mm Pitch, Micro-Lock Plus Single Row Plug Housings	<u>213719</u>

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for Micro-Lock Plus 2.0 Crimp Terminals, 24-22 AWG, UL1061 Wire	<u>2130694500</u>
FA2 Pneumatic Feed Crimp Applicator for Micro-Lock Plus 2.0 Crimp Terminals, 24-22 AWG, UL1061 Wire	<u>2130694510</u>
FA2 Mechanical Feed Crimp Applicator for Micro-Lock Plus Male Crimp Terminals, 26 AWG, UL1061 Wire	<u>2130694600</u>
FA2 Pneumatic Feed Applicator for Micro-Lock Plus Male Crimp Terminals, 26 AWG, UL1061 Wire	<u>2130694610</u>
Hand Crimp Tool for Micro-Lock Plus Male Crimp Terminals, 26-22 AWG, UL1061 Wire	<u>2133095900</u>
Extraction Tool for Micro-Lock Plus 2.00mm Pitch Male Crimp Terminals	<u>2002221900</u>

Japan

Description	Part Number
S-1 Applicator for Micro-Lock Plus 2.00mm Pitch Plug Terminals, 26-22	<u>2168013700</u>

AWG (UL 1061)	
Hand Extraction Tool for Micro-Lock Plus 2.00mm Pitch Plug and Terminal	<u>2168016000</u>