



Part Number : [351500614](#)
Product Description : VersaBlade Hybrid Receptacle
Housing, with Mounting Ears, 6 Circuits, Blue
Series Number : 35150
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

[351500614_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS_ENG-000.pdf](#)

[351500000AS_KOR-000.pdf](#)

[PK-35150-005-001.pdf](#)

[PS-35150-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35150
Description	VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	800754834889

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Blue
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None

Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	6.160/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	7.30mm
Pitch - Termination Interface	7.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Hybrid Plug Housings	<u>35151</u>

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Natural	<u>351500390</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Red	<u>351500392</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow	<u>351500393</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Blue	<u>351500394</u>
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<u>2270288400</u>
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	<u>2270298400</u>
VersaBlade Male Crimp Terminals	<u>35745</u>

VersaBlade Female Crimp Terminals	<u>35746</u>
VersaBlade Male Crimp Terminals	<u>35747</u>