



**Part Number :** [2185101041](#)

**Product Description :** Milli-Grid-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Dual Row, 100.00mm Length, 4 Circuits, Black

**Series Number :** 218510

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies



## Documents & Resources

### Drawings

[2185101041 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                                 |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                                           |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                                               |
| EU RoHS            | Compliant per EU 2015/863                                                                                    |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

|                        |                                                                                                                      |
|------------------------|----------------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                               |
| Category               | Power and Signal Cable Assemblies                                                                                    |
| Series                 | 218510                                                                                                               |
| Description            | Milli-Grid-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Dual Row, 100.00mm Length, 4 Circuits, Black |
| Assembly Configuration | Single Ended Connector                                                                                               |
| Connector to Connector | N/A                                                                                                                  |
| Product Name           | Milli-Grid                                                                                                           |
| Type                   | Discrete Wire Assembly                                                                                               |
| UPC                    | 195842350915                                                                                                         |

**Electrical**

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 2.0A             |
| Voltage - Maximum             | 125V AC (RMS)/DC |

**Physical**

|                     |                |
|---------------------|----------------|
| Cable Length        | 100.00mm       |
| Circuits (Loaded)   | 4              |
| Circuits (maximum)  | 4              |
| Color - Resin       | Black          |
| Gender              | Female-Pigtail |
| Lock to Mating Part | Yes            |
| Material - Metal    | Copper Alloy   |

|                             |                      |
|-----------------------------|----------------------|
| Material - Plating Mating   | Matte Tin            |
| Material - Resin            | Polyester            |
| Net Weight                  | 1.188/g              |
| Number of Rows              | 2                    |
| Packaging Type              | Bag                  |
| Pitch - Mating Interface    | 2.00mm               |
| Single Ended                | Yes                  |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type             | UL 10002             |
| Wire Size (AWG)             | 24                   |

---

This document was generated on Sep 23, 2025