



Part Number : [314049116](#)

Product Description : 2.54mm MX64 Sealed Crimp Housing, Single Row, TE Generation Y Terminal, Black, 8 Circuits, Key A, with CPA Lock, Terminals 2, 4, 5, 6, 7, and 8 Plugged

Series Number : 31404

Status : Active

Product Category : Connector Housings

Engineering Number : CVP314049116



Documents & Resources

Drawings

[314049116_sd.pdf](#)

[PK-31300-256-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[314020000-000.pdf](#)

[AS-31402-000-001.pdf](#)

[PS-31404-001-1X8-001.pdf](#)

[314040003-000.pdf](#)

[TS-31404-001-1X8-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains

	Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	31404
Description	2.54mm MX64 Sealed Crimp Housing, Single Row, TE Generation Y Terminal, Black, 8 Circuits, Key A, with CPA Lock, Terminals 2, 4, 5, 6, 7, and 8 Plugged
Application	Power, Wire-to-Board
Product Name	MX64
UPC	191128779272

Physical

Circuits (maximum)	8
Color - Resin	Black

Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	9.356/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarization	A
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Sensors, Other USCAR Interfaces

Use with Part(s)

Description	Part Number
MX64 Wire Dress Covers	<u>31414</u>
Use With	TE Connectivity Generation Y 0.64mm