




**Part Number :** [395145018](#)

**Product Description :** 3.81mm Pitch Eurostyle  
Horizontal Plug, with Retention Screws, Green  
Housing, 18 Circuits

**Series Number :** 39514

**Status :** Active

**Product Category :** Terminal Blocks and Barrier  
Strip



---

## Documents and Resources

### Drawings

[395145018 sd.pdf](#)

[PK-39500-001-001.pdf](#)

[PK-39514-001-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | Not Relevant                                   |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                 |
| REACH SVHC         | Contains Lead per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863  |

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                           |
|----------------|-------------------------------------------------------------------------------------------|
| Status         | Active                                                                                    |
| Category       | Terminal Blocks and Barrier Strip                                                         |
| Series         | 39514                                                                                     |
| Description    | 3.81mm Pitch Eurostyle Horizontal Plug, with Retention Screws, Green Housing, 18 Circuits |
| Application    | Wire-to-Board                                                                             |
| Component Type | Plug                                                                                      |
| Product Name   | Eurostyle Pluggable                                                                       |
| Type           | PCB Terminal Blocks and Connectors                                                        |
| UPC            | 822350690195                                                                              |

### Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum             | 300V |

### Physical

|                               |                    |
|-------------------------------|--------------------|
| Circuits (Loaded)             | 18                 |
| Circuits (maximum)            | 18                 |
| Color - Resin                 | Green              |
| Entry Angle                   | Vertical           |
| Lock to Mating Part           | Yes                |
| Net Weight                    | 15.560/g           |
| Number of Rows                | 1                  |
| Orientation                   | N/A                |
| Panel Mount                   | No                 |
| PCB Retention                 | N/A                |
| Pitch - Mating Interface      | 3.81mm             |
| Pitch - Termination Interface | 3.81mm             |
| Polarized to Mating Part      | Yes                |
| Stackable                     | No                 |
| Temperature Range - Operating | -40° to +105°C     |
| Wire Size (AWG)               | 16, 18, 20, 22, 24 |
| Wire Size mm <sup>2</sup>     | 0.20-1.31          |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                   | Part Number                                     |
|-----------------------------------------------|-------------------------------------------------|
| 3.81mm Pitch Eurostyle Vertical PCB Headers   | <a href="#"><u>39515</u></a>                    |
| 3.81mm Pitch Eurostyle Horizontal PCB Headers | <a href="#"><u>39516</u></a>                    |
| Mates With                                    | Most 3.81mm Pitch Industry Standard PCB Headers |