



Part Number : [367831212](#)

Product Description : MX120G Sealed Header
Connector Assembly, 12 Circuit, Gray Housing with No
Color Mark

Series Number : 36783

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[367831212_sd.pdf](#)

[PK-36783-001-001.pdf](#)

Specifications

[AS-36783-001-001.pdf](#)

[PS-36783-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	36783
Description	MX120G Sealed Header Connector Assembly, 12 Circuit, Gray Housing with No Color Mark
Application	Wire-to-Board
Component Type	PCB Header
Product Name	MX120G
UPC	191128460958

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	10.5A
Voltage - Maximum	36V DC

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94HB

Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	8.783/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.20mm
Pitch - Mating Interface	3.20mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	None
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX120G Pitch Sealed Female Connector Assembly, Dual Row, 12 Circuit, Gray	<u>367921206</u>