



**Part Number :** [395260019](#)

**Product Description :** 5.00mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, 19 Circuits

**Series Number :** 39526

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip



---

## Documents and Resources

### Drawings

[395260019 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | Not Reviewed per SJ/T 11365-2006               |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                |
| REACH SVHC         | Contains Lead per D(2025)6375-DC (05 Nov 2025) |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863  |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                             |
|----------------|---------------------------------------------------------------------------------------------|
| Status         | Active                                                                                      |
| Category       | Terminal Blocks and Barrier Strip                                                           |
| Series         | 39526                                                                                       |
| Description    | 5.00mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, 19 Circuits |
| Application    | Wire-to-Board                                                                               |
| Component Type | PCB Header                                                                                  |
| Product Name   | Eurostyle Pluggable                                                                         |
| Type           | PCB Terminal Blocks and Connectors                                                          |
| UPC            | 822350503587                                                                                |

### Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 15.0A |
| Voltage - Maximum             | 300V  |

### Physical

|                               |                |
|-------------------------------|----------------|
| Circuits (Loaded)             | 19             |
| Circuits (maximum)            | 19             |
| Color - Resin                 | Black          |
| Entry Angle                   | N/A            |
| Lock to Mating Part           | Yes            |
| Number of Rows                | 1              |
| Orientation                   | Horizontal     |
| Panel Mount                   | No             |
| PCB Thickness - Recommended   | 3.20mm         |
| PC Tail Length                | 3.90mm         |
| Pitch - Mating Interface      | 5.00mm         |
| Pitch - Termination Interface | 5.00mm         |
| Polarized to Mating Part      | Yes            |
| Shrouded                      | Closed Ends    |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size (AWG)               | N/A            |

### Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

---

## Mates With / Use With

### Mates with Part(s)

| Description                             | Part Number                               |
|-----------------------------------------|-------------------------------------------|
| 5.00mm Pitch Eurostyle Horizontal Plugs | <u>39524</u>                              |
| 5.00mm Pitch Eurostyle Plugs            | <u>39527</u>                              |
| Mates With                              | Most 5.00mm Pitch Industry Standard Plugs |