



**Part Number :** [395338505](#)  
**Product Description :** 5.08mm Pitch Eurostyle  
Vertical Plug, Front Wire Entry, Green Housing, Gold  
(Au) Plated, 5 Circuits  
**Series Number :** 39533  
**Status :** Active  
**Product Category :** Terminal Blocks and Barrier  
Strip

---

**Documents and Resources**

**Drawings**  
[395338505 sd.pdf](#)  
[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)

**Specifications**  
[PS-39500-001-001.pdf](#)

---

**Product Environment Compliance**

**Compliance**

|                    |                                               |
|--------------------|-----------------------------------------------|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Not Reviewed per EU 2015/863                  |

- Compliance Statements
- EU RoHS
  - REACH SVHC
  - Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

# Part Details

## General

|                |                                                                                                     |
|----------------|-----------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                              |
| Category       | Terminal Blocks and Barrier Strip                                                                   |
| Series         | 39533                                                                                               |
| Description    | 5.08mm Pitch Eurostyle Vertical Plug, Front Wire Entry, Green Housing, Gold (Au) Plated, 5 Circuits |
| Application    | Wire-to-Board                                                                                       |
| Comments       | Front Wire Entry                                                                                    |
| Component Type | Plug                                                                                                |
| Product Name   | Eurostyle Pluggable                                                                                 |
| Type           | PCB Terminal Blocks and Connectors                                                                  |
| UPC            | 822350535793                                                                                        |

## Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 18.0A |
| Voltage - Maximum             | 300V  |

## Physical

|                     |            |
|---------------------|------------|
| Circuits (Loaded)   | 5          |
| Color - Resin       | Green      |
| Entry Angle         | Horizontal |
| Lock to Mating Part | Yes        |

|                               |                                |
|-------------------------------|--------------------------------|
| Number of Rows                | 1                              |
| Orientation                   | N/A                            |
| Panel Mount                   | No                             |
| PCB Retention                 | N/A                            |
| Pitch - Mating Interface      | 5.08mm                         |
| Pitch - Termination Interface | 5.08mm                         |
| Polarized to Mating Part      | Yes                            |
| Stackable                     | No                             |
| Temperature Range - Operating | -40° to +105°C                 |
| Wire Size (AWG)               | 12, 14, 16, 18, 20, 22, 24, 26 |
| Wire Size mm <sup>2</sup>     | 0.13-3.31                      |

### Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

---

## Mates With / Use With

### Mates with Part(s)

| Description                                   | Part Number                                     |
|-----------------------------------------------|-------------------------------------------------|
| 5.08mm Pitch Eurostyle Vertical PCB Headers   | <a href="#"><u>39531</u></a>                    |
| 5.08mm Pitch Eurostyle Horizontal PCB Headers | <a href="#"><u>39532</u></a>                    |
| 5.08mm Pitch Eurostyle Dual Level PCB Headers | <a href="#"><u>39538</u></a>                    |
| Mates With                                    | Most 5.08mm Pitch Industry Standard PCB Headers |