










奇数キャビティ：キャビティ番号及び金型番号
偶数キャビティ：トレードマーク

ODD CAV:CAVITY & MOLD NUMBER
EVEN CAV:TRADE MARK

奇数キャビティ：トレードマーク
偶数キャビティ：キャビティ番号及び金型番号

ODD CAV:TRADE MARK
EVEN CAV:CAVITY & MOLD NUMBER



ターミナル装着図
TERMINAL ASSEMBLY DRAWING

注記：

NOTES：

① 材質：TABLE 1参照
MATERIAL：SEE TABLE 1.

② 偶数極に適用。
APPLY FOR EVEN CIRCUIT.

③ 製品仕様書、コネクタ取扱説明書、適合嵌合相手、
PLEASE REFER TO SHEET 3 FOR PRODUCT SP
MATE WITH AND APPLICABLE TERMINAL.

④ 発注番号：SHEET 3 参照
ORDER NUMBER：PLEASE REFER TO SHEET 3

505565**0*

極数
CIRCUIT SIZE

番号 NO.	ハウジングカラー HOUSING COLOR
0	ナチュラル (白) NATURAL (WHITE)
1	黒 BLACK
2	赤 RED
3	黄 YELLOW
4	青 BLUE
6	緑 GREEN
8	橙 ORANGE


18.75	22	16
17.50	20.75	15
16.25	19.5	14
15	18.25	13
13.75	17	12
12.5	15.75	11
11.25	14.5	10
10	13.25	9
8.75	12	8
7.5	10.75	7
6.25	9.5	6
5	8.25	5
3.75	7	4
2.5	5.75	3
1.25	4.5	2
B	A	極数 CIRCUIT SIZE

 TABLE 1


部品 PART	材質 MATERIAL				
ハウジング HOUSING	ポリエステル(PBT), UL94 V-0, 色 : SHEET 3参照 POLYESTER(PBT), UL94 V-0, COLOR : SEE SHEET 3.				
DOCUMENT STATUS	P1	RELEASE DATE	2025/02/25	06:03:52	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515932.			molex						
mm		NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED)		MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING											
ANGULAR TOL ± 3.0 °													
4 PLACES ± 0.2		EC NO: 812554			PRODUCT CUSTOMER DRAWING								
3 PLACES ± 0.2		DRWN: RAVINR1 2025/01/27											
2 PLACES ± 0.2		CHK'D: GGA 2025/02/25											
1 PLACE ± 0.2		APPR: GGA 2025/02/25			DOCUMENT NUMBER		DOC TYPE		DOC PART		REVIS		
0 PLACES ± 0.2		INITIAL REVISION:											5055650002-SD
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A3-SIZE		505565		SEE TABLE		GENERAL		1 OF 3	

製品形状
PRODUCT SHAPE




VIEW Z




VIEW Z

2-13極
2-13 CIRCUIT



VIEW Y



VIEW Y

14-16極
14-16 CIRCUIT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515932.			molex				
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING							
ANGULAR TOL ± 3.0°											
4 PLACES		± 0.2		EC NO: 812554			PRODUCT CUSTOMER DRAWING				
3 PLACES		± 0.2		DRWN: RAVINR1 2025/01/27							
2 PLACES		± 0.2		CHK'D: GGA 2025/02/25							
1 PLACE		± 0.2		APPR: GGA 2025/02/25			DOCUMENT NUMBER 5055650002-SD				
0 PLACES		± 0.2		INITIAL REVISION: DRWN: RWATANABE01 2017/09/14						DOC TYPE PSD	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		DOC PART 000		REVISION H1	
						A3-SIZE		SHEET NUMBER 2 OF 3			
				SERIES 505565		MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL			


△₃ 適合製品及び各種仕様書 APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

梱包仕様書 PACKAGING SPECIFICATION	PART NUMBER		SPECIFICATION NUMBER		
	505565**0*		5055659200 PS 200		
適合ターミナル APPLICABLE TERMINAL	PART NUMBER		PLATING TYPE		WIRE SIZE(AWG)
	5054311000		TIN		#26-30
	5054311*00 1,2,3 ▲		GOLD		
適合嵌合相手 MATE WITH	WIRE TO BOARD				WIRE TO WIRE
	TIN PLATING		GOLD PLATING		TIN PLATING
	VERTICAL	RIGHT ANGLE	VERTICAL	RIGHT ANGLE	---
	2-16CKT				2-9CKT
シリーズ番号 SERIES NUMBER	505568**7*	505567**7*	505568**** 3,5,8 ▲	505567**** 3,5,8 ▲	2145252***
製品仕様書 PRODUCT SPECIFICATION	5055650000 PS 000		5055650002 PS 000		5055650003-PS PS 000
コネクタ取扱説明書 APPLICATION SPECIFICATION	5055650000-AS PS 000				

製品嵌合図は各嵌合相手図面を参照のこと
MATING VIEW : REFER TO EACH "MATE WITH" PART DRAWING.

△₄ 505565**0* 発注番号一覧 ORDER NUMBER LIST

ORANGE	GREEN	BLUE	YELLOW	RED	BLACK	NATURAL (WHITE)	HOUSING COLOR
-----	-----	5055651604	-----	5055651602	5055651601	5055651600	16
-----	-----	5055651504	-----	5055651502	5055651501	5055651500	15
-----	-----	5055651404	-----	5055651402	5055651401	5055651400	14
-----	-----	5055651304	-----	5055651302	5055651301	5055651300	13
-----	-----	5055651204	-----	5055651202	5055651201	5055651200	12
-----	-----	5055651104	-----	5055651102	5055651101	5055651100	11
-----	-----	5055651004	-----	5055651002	5055651001	5055651000	10
-----	5055650906	5055650904	-----	5055650902	5055650901	5055650900	9
-----	-----	5055650804	5055650803	5055650802	5055650801	5055650800	8
-----	-----	5055650704	-----	5055650702	5055650701	5055650700	7
-----	-----	5055650604	-----	5055650602	5055650601	5055650600	6
-----	-----	5055650504	-----	5055650502	5055650501	5055650500	5
5055650408	5055650406	5055650404	5055650403	5055650402	5055650401	5055650400	4
-----	-----	5055650304	-----	5055650302	5055650301	5055650300	3
5055650208	5055650206	5055650204	5055650203	5055650202	5055650201	5055650200	2
発注番号 ORDER NUMBER							極数 CIRCUIT SIZE
梱包形態：ポリ袋 PACKAGING：POLYBAG PACKAGE							

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515932.				molex					
mm		NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 812554 DRWN: RAVINR12025/01/27 CHK'D: GGA2025/02/25 APPR: GGA2025/02/25				MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING					
ANGULAR TOL ± 3.0 °													
4 PLACES		± 0.2						PRODUCT CUSTOMER DRAWING					
3 PLACES		± 0.2											
2 PLACES		± 0.2						DOCUMENT NUMBER 5055650002-SD					
1 PLACE		± 0.2		PSD	000	H1							
0 PLACES		± 0.2											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING A3-SIZE		SERIES 505565	MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL	SHEET NUMBER 3 OF 3	

DOCUMENT STATUS	P1	RELEASE DATE	2025/02/25	06:03:52
-----------------	----	--------------	------------	----------