




**Part Number :** [522072360](#)

**Product Description :** Easy-On FFC/FPC Connector,  
1.00mm Pitch, Slider Series, Right-Angle, Top Contact,  
2.70mm Height, 23 Circuits, Gold Plating

**Series Number :** 52207

**Status :** Active

**Product Category :** FFC / FPC Connectors



## Documents & Resources

### Drawings

[522072360 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[522072360.dxf](#)

### Specifications

[2297470000-AS-JP.pdf](#)

[SPK-52207-002-001.pdf](#)

[PS-52207-048-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                           |
|--------------------|-----------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Compliant with Exemption 44; 33                                                                           |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                              |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                                        |
| REACH SVHC         | Not Contained per D(2025)4165-DC (25 June 2025)                                                           |
| EU RoHS            | Compliant per EU 2015/863                                                                                 |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

|              |                                                                                                                            |
|--------------|----------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                     |
| Category     | FFC / FPC Connectors                                                                                                       |
| Series       | Slider                                                                                                                     |
| Description  | Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 23 Circuits, Gold Plating |
| Product Name | Easy-On                                                                                                                    |
| UPC          | 822350134002                                                                                                               |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum             | 125V |

### Physical

|               |        |
|---------------|--------|
| Actuator Type | Slider |
|---------------|--------|

|                                |                       |
|--------------------------------|-----------------------|
| Circuits (Loaded)              | 23                    |
| Color - Resin                  | Natural               |
| Contact Position               | Top                   |
| Durability (mating cycles max) | 30                    |
| Flammability                   | 94V-0                 |
| Mated Height                   | 2.70mm                |
| Material - Metal               | Phosphor Bronze       |
| Material - Plating Mating      | Gold                  |
| Material - Plating Termination | Tin                   |
| Material - Resin               | Nylon                 |
| Orientation                    | Right Angle           |
| Packaging Type                 | Embossed Tape on Reel |
| PCB Locator                    | No                    |
| PCB Mounting                   | Surface Mount         |
| PCB Retention                  | Yes                   |
| PC Tail Length                 | 2.00mm                |
| Pitch - Mating Interface       | 1.00mm                |
| Pitch - Termination Interface  | 1.00mm                |
| Polarized to PCB               | Yes                   |
| Stackable                      | No                    |
| Temperature Range - Operating  | -40° to +85°C         |
| Wire/Cable Type                | FFC/FPC               |

---

## Mates With / Use With

### Mates with Part(s)

| Description                         | Part Number  |
|-------------------------------------|--------------|
| 1.00mm Pitch Premo-Flex FFC Jumpers | <u>15039</u> |